




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	09/30/2022	GUTTADAURO



PART NUMBER	LENGTH METERS [FEET]
CAU3HFA-90UB-05M	0.5 [1.64]
CAU3HFA-90UB-1M	1.0 [3.28]
CAU3HFA-90UB-105M	1.5 [4.92]
CAU3HFA-90UB-2M	2.0 [6.56]
CAU3HFA-90UB-205M	2.5 [8.20]

NOTES:

- CABLE TYPE-U DRAG CHAIN TESTING: 5 MILLION CYCLES MIN.(75mm BEND RADIUS)
- CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
- CABLE ASSEMBLY SHALL MEET USB 3.0 REQUIREMENTS.
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13] THIRD-ANGLE PROJECTION 	APPROVALS	DATE	 an INFINITI® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936				
	DRAWN BY SLI	01/19/2022			CATEGORY		
	CHECKED BY GUTTADAURO	01/19/2022					
	APPROVED BY GUTTADAURO	01/19/2022					
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			PRODUCT DESCRIPTION				
			CA HI-FLEX USB3.0 A/90UP B				
COLOR VARIATIONS MAY OCCUR			SIZE A	CAGE CODE 43321	DWG. NO. CAU3HFA-90UB	REV. A	
			SCALE: NONE			CAD FILE: CAU3HFA-90UB.SLDDRW	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[L-Com:](#)

[CAU3HFA-90UB-05M](#) [CAU3HFA-90UB-105M](#) [CAU3HFA-90UB-2M](#) [CAU3HFA-90UB-1M](#) [CAU3HFA-90UB-205M](#)