



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC.. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/8/12	D.GRIFFIN
B	ECN 7489: UPDATE RECOMMENDED PANEL CUTOUT DIMS, UPDATE ROHS NOTE	6/16/14	S.LI




LENGTH CODE CHART		
CABLE# & LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED
CA-MMNFBCXXX	WHERE XXX = LENGTH IN FEET	CA-MMNFBC010 (10 FEET)
CA-MMNFBCNXX	WHERE NXX = LENGTH IN INCHES	CA-MMNFBCN16 (16 INCHES)
CA-MMNFBCMXX	WHERE MXX = LENGTH IN METERS	CA-MMNFBCM07 (7 METERS)
CA-MMNFBCXMX	WHERE XMX = LENGTH IN DECIMAL METERS	CA-MMNFBC3M5 (3.5 METERS)



NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL RECEIVE INSERTION LOSS TEST PER L-COM SPECIFICATIONS.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		CATEGORY COAXIAL	
	DRAWN BY D.FRISIELLO	10/5/12				
	CHECKED BY T.VADEN	10/5/12	PRODUCT DESCRIPTION CA,CA-100 MMCX/NF BLKHD			
	APPROVED BY P.PESA	10/5/12				
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE	FSCM NO.	DWG. NO.	REV.
	COLOR VARIATIONS MAY OCCUR		A	43321	CA-MMNFBC	B
			SCALE: NONE	CAD FILE: CA-MMNFBC.SLDRW	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[L-Com:](#)

[CA-MMNFBCN19](#)