


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	9/24/10	D.GRIFFIN
B	ECN 5210: ADDED WIRE MAP, HARDWARE NOTES & HOOD DIMS., DETAIL VIEW	12/15/10	D. CASTRO





MODEL NUMBER	LENGTH	
	FEET	METERS
CPMS9MF-1	1.0	.30
CPMS9MF-2.5	2.5	.76
CPMS9MF-5	5.0	1.52
CPMS9MF-10	10.0	3.05
CPMS9MF-25	25.0	7.62
CPMS9MF-50	50.0	15.24

NOTES:

SUPPLIED WITH THUMBSCREWS IN PLACE.  
NOTE: SUPPLIED WITH OPTIONAL USE HARDWARE AND INSTRUCTIONS.  
CABLE INTERCONNECTION HARDWARE: (4) SCREWLOCKS, H= .191"  
PANEL MOUNT HARDWARE: (4) SCREWLOCKS, H= .160"

CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.

CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%  ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS	DATE	 <div>45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845</div>				
	DRAWN BY D.FRISIELLO	9/7/10		CATEGORY  DATA CABLING			
	CHECKED BY S.SMITH	9/7/10					
	APPROVED BY S.SMITH	9/7/10					
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION  20AWG DATA CABLE ASSEMBLY				
	COLOR VARIATIONS MAY OCCUR			SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>CPMS9MF</b>	REV. <b>B</b>
				SCALE: NONE	CAD FILE: CPMS9MF.SLDDRW		SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[infinite Electronics:](#)

[CPMS9MF-2.5](#) [CPMS9MF-25](#) [CPMS9MF-50](#) [CPMS9MF-10](#) [CPMS9MF-5](#) [CPMS9MF-1](#)