


RoHS Compliant ✓

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN #3360, CN RELEASE	6/03/08	E. STAUBLE
F	ECN 4474: ADDED 1.0 FT. LENGTH, UPDATED FORMAT, ADDED NOTES	1/7/10	D. CASTRO
G	ECN4813: ADDED 26AWG & PANTONE 400C TO CABLE DESCRIPTION. ADDED LOGO NOTE.	6/14/10	DFP



"P1"	WIRE COLOR	"P2"
1	BLACK	1
2	BROWN	2
3	RED	3
4	ORANGE	4
5	YELLOW	5
6	GREEN	6
7	BLUE	7
8	VIOLET	8
9	GRAY	9
10	WHITE	10
11	PINK	11
12	LIGHT GREEN	12
13	BLACK / WHITE	13
14	BROWN / WHITE	14
15	RED/ WHITE	15
SHELL	DRAIN WIRE	SHELL

MODEL NUMBER	LENGTH	
	FEET	METERS
CS2H15MM-1	1.0	0.31
CS2H15MM-2.5	2.5	0.76
CS2H15MM-5	5.0	1.52
CS2H15MM-6	6.0	1.83
CS2H15MM-10	10.0	3.05
CS2H15MM-12	12.0	3.66
CS2H15MM-15	15.0	4.57
CS2H15MM-25	25.0	7.62
CS2H15MM-50	50.0	15.24

NOTES:

- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPEC. PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY TJC	9/28/01		
	CHECKED BY DFP	9/28/01	CATEGORY	D-SUBMINIATURE
	APPROVED BY RC	10/3/01	PRODUCT DESCRIPTION	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CABLE, HD15M/M DBL SHLD	
	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. CS2H15MM
	SCALE: NONE		CAD FILE: CS2H15MM.SLDDRW	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[L-Com:](#)

[CS2H15MM-5](#) [CS2H15MM-15](#) [CS2H15MM-25](#) [CS2H15MM-1](#) [CS2H15MM-50](#) [CS2H15MM-2.5](#) [CS2H15MM-12](#)
[CS2H15MM-6](#) [CS2H15MM-10](#)