


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
L	ECN 7298: REVISE MOLDED HOOD, FORMAT, ROHS, CBL DESCRIPTION	2/18/14	D.FRISIELLO





"P1"	WIRE COLOR	"J1"
1	BLACK	1
2	BROWN	2
3	RED	3
4	ORANGE	4
5	YELLOW	5
6	GREEN	6
7	BLUE	7
8	VIOLET	8
9	GRAY	9
10	WHITE	10
11	PINK	11
12	PINK/BLACK	12
13	LIGHT GREEN	13
14	BLACK/WHITE	14
15	BROWN/WHITE	15
16	RED/WHITE	16
17	ORANGE/WHITE	17
18	GREEN/WHITE	18
19	BLUE/WHITE	19
20	VIOLET/WHITE	20
21	RED/BLACK	21
22	ORANGE/BLACK	22
23	YELLOW/BLACK	23
24	GREEN/BLACK	24
25	GRAY/BLACK	25
SHELL	DRAIN WIRE	SHELL

MODEL NUMBER	LENGTH	
	(FEET)	(METERS)
CS2N25MF-1	1.0	0.31
CS2N25MF-2.5	2.5	0.76
CS2N25MF-5	5.0	1.52
CS2N25MF-6	6.0	1.83
CS2N25MF-10	10.0	3.05
CS2N25MF-12	12.0	3.66
CS2N25MF-15	15.0	4.57
CS2N25MF-25	25.0	7.62
CS2N25MF-50	50.0	15.24

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ±.005 [1.3]	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845			
	DRAWN BY TJC	9/27/01				
	CHECKED BY DFP	9/28/01	CATEGORY	D-SUBMINIATURE		
	APPROVED BY RC	10/4/01	PRODUCT DESCRIPTION		CABLE, DB25M/F DBL SHLD	
PROJECTION 	COLOR VARIATIONS MAY OCCUR		SIZE A	FSCM NO. 43321	DWG. NO. CS2N25MF	REV. L
			SCALE: NONE		CAD FILE: CS2N25MF.SLDRW	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[infinite Electronics:](#)

[CS2N25MF-10](#) [CS2N25MF-1](#) [CS2N25MF-50](#) [CS2N25MF-15](#) [CS2N25MF-5](#) [CS2N25MF-2.5](#) [CS2N25MF-12](#)
[CS2N25MF-6](#) [CS2N25MF-25](#)