


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
B	ECN #3382, UPDATED DWG FORMAT, ADDED WIRING MAP, REVISED MODEL	6/9/08	E. STAUBLE
H	ECN 4474: ADDED 1.0 FT LENGTH, UPDATED FORMAT, ADDED NOTES & RoHS	1/7/10	D. CASTRO
J	ECN4813: ADDED 26AWG & PANTONE 400C TO CABLE DESCRIPTION, ADDED LOGO NOTE	6/9/10	DFP



WIRING MAP					
"P1"	WIRE COLOR	"J1"	"P1"	WIRE COLOR	"J1"
1	BROWN	1	20	GRAY / GREEN	20
2	RED	2	21	GRAY / RED	21
3	ORANGE	3	22	GRAY / VIOLET	22
4	YELLOW	4	23	LIGHT GREEN / BLACK	23
5	GREEN	5	24	RED/BLACK	24
6	BLUE	6	25	ORANGE / BLACK	25
7	VIOLET	7	26	YELLOW / BLACK	26
8	GRAY	8	27	GREEN / BLACK	27
9	WHITE	9	28	LIGHT BLUE / BLACK	28
10	LIGHT GREEN	10	29	LIGHT BLUE / BROWN	29
11	BLACK	11	30	LIGHT BLUE / VIOLET	30
12	GRAY / BLACK	12	31	LIGHT BLUE / RED	31
13	BLUE / WHITE	13	32	LIGHT BLUE	32
14	VIOLET / WHITE	14	33	PINK	33
15	BROWN / WHITE	15	34	PINK / BLACK	34
16	BLACK / WHITE	16	35	PINK / GREEN	35
17	RED / WHITE	17	36	PINK / VIOLET	36
18	ORANGE / WHITE	18	37	PINK / RED	37
19	GREEN / WHITE	19	SHELL	DRAIN WIRE	SHELL

MODEL NUMBER	LENGTH	
	FEET	METERS
CS2N37MF-1	1.0	0.31
CS2N37MF-2.5	2.5	0.76
CS2N37MF-5	5.0	1.52
CS2N37MF-10	10.0	3.05
CS2N37MF-15	15.0	4.57
CS2N37MF-25	25.0	7.62
CS2N37MF-50	50.0	15.24

- NOTES:
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPEC. PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]

OVERALL CABLE LENGTH TOLERANCE:
≤12 [305] = +1 [25] / -0
>12 [305] ≤60 [1524] = +2 [51] / -0
>60 [1524] ≤120 [3048] = +4 [102] / -0
>120 [3048] ≤300 [7620] = +6 [152] / -0
>300 [7620] = +3% / -0%

ALL OTHER DIMENSIONAL TOLERANCES:
.X = ± .2
.XX = ± .02
.XXX = ± .005

PROJECTION

APPROVALS

DRAWN BY	TJC
CHECKED BY	DFP
APPROVED BY	RC

DATE

9/28/01
9/28/01
10/3/01

L-com Global Connectivity

45 BEECHWOOD DRIVE
NORTH ANDOVER, MA
01845

CATEGORY

D-SUBMINIATURE

PRODUCT DESCRIPTION

CABLE, DB37M/F DBL SHLD

SIZE **A** FSCM NO. **43321** DWG. NO. **CS2N37MF** REV. **J**

SCALE: NONE CAD FILE: CS2N37MF.SLDRW SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[infinite Electronics:](#)

[CS2N37MF-50](#) [CS2N37MF-10](#) [CS2N37MF-2.5](#) [CS2N37MF-5](#) [CS2N37MF-15](#) [CS2N37MF-1](#) [CS2N37MF-25](#)