



8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC.. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
C	ECN 5868: ADDED LENGTHS 03 M, 075 M, REVISED WIRE MAP	12/7/11	D.FRISIELLO
D	ECN5915: REVISED VIEWS OF USB MICRO B MALE	01/10/12	DFP
E	ECN6237: ADDED CONTACT PLATING NOTE, UPDATED FORMAT.	09/17/12	DFP
E	ECN 999999: UPDATE TO CORRECT ORIENTATION OF LOGO ON MICRO B END	1/13/16	S.LI



MODEL NUMBER	LENGTH METERS [FEET]
CSMUAMICB-03M	0.3 [.98]
CSMUAMICB-05M	0.5 [1.64]
CSMUAMICB-075M	0.75 [2.46]
CSMUAMICB-1M	1.0 [3.28]
CSMUAMICB-2M	2.0 [6.56]
CSMUAMICB-3M	3.0 [9.84]



NOTES:

1. CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
2. CABLE ASSEMBLY SHALL MEET USB 2.0 REQUIREMENTS.
3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [13] PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY D. PARHAM	06/03/2010		
	CHECKED BY D. CASTRO	06/03/2010	CATEGORY USB	
	APPROVED BY S. SMITH	06/03/2010	PRODUCT DESCRIPTION CBL, USB-A/MICRO B	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321	DWG. NO. CSMUAMICB
COLOR VARIATIONS MAY OCCUR		SCALE: NONE	CAD FILE: CSMUAMICB.SLDDRW	REV. E
		SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[infinite Electronics:](#)

[CSMUAMICB-05M](#) [CSMUAMICB-1M](#) [CSMUAMICB-03M](#) [CSMUAMICB-2M](#) [CSMUAMICB-3M](#) [CSMUAMICB-075M](#)