


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE  
PROPERTY OF L-COM, INC., ANY REPRODUCTION IN PART OR WHOLE  
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/08/03	B.MAZEJKA
B	ECN3196: UPDATE DWG FORMAT	2/13/08	D.GRIFFIN
C	ECN3680, ADDED PACKAGING TABLE	2008.10.30	E. STAUBLE
C	ECN999999: REMOVED PACKAGE IN POLYBAG NOTE	11/10/08	D.GRIFFIN



#### NOTES:

#### MATERIAL:

SHELL: STEEL

INSULATOR: PBT W/GLASS FIBER FILL (UL 94V-0 RATED)

#### FINISH:

FRONT SHELL: BRIGHT TIN/NICKEL PLATED

REAR SHELL: BRIGHT TIN PLATED

CATALOG #	PACKAGING
C&P25M	1/BAG
C&P25M-TRAY	50/TRAY

**RoHS Compliant** ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  OVERALL CABLE LENGTH TOLERANCE: >12 [305] - ≤12 [305] = +1 [25] / -0 >60 [1524] - 60 [1524] = +2 [51] / -0 >120 [3048] - 120 [3048] = +4 [102] / -0 >300 [7620] - 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%  ALL OTHER DIMENSIONAL TOLERANCES: .X = .3 .XX = .15  PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY B.MAZEJKA	11/10/2003		
	CHECKED BY C.McCORMICK	12/08/2003	CATEGORY DSUB	
	APPROVED BY D.PARHAM	12/08/2003	PRODUCT DESCRIPTION DB25M CRIMP & POKE CONNECTOR	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. C&P25M
COLOR VARIATIONS MAY OCCUR		REF	SCALE: NONE	CAD FILE: C&P25M.SLDDRW
				SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[infinite Electronics:](#)

[C&P25M-TRAY](#) [C&P25M](#)