




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	DRAWING REPLACES DMA010MF-OD1	8/23/12	D.FRISIELLO



RECOMMENDED
PANEL OPENING
MAX PANEL THICKNESS: 0.06"

MALE, 9 PIN
D-SUB CONNECTOR

PIN 1



FEMALE, 25 PIN
D-SUB CONNECTOR

PIN 1

SPECIFICATIONS;

MATERIALS;

SHELL: COLD ROLLED STEEL
CONTACTS: BRASS
INSULATOR: PBT UL94-V0 RATED

FINISH;

SHELL: TIN PLATED
CONTACT: GOLD FLASH


MISCELLANEOUS:

COMPONENTS SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES (mm)
OVERALL CABLE LENGTH TOLERANCE:
≤12 (305) ±.1 (25) / -0
>12 (305) ≤60 (1524) = +.25(1) / -0
>60 (1524) ≤120 (3048) = +.4 (102) / -0
>120 (3048) ≤300 (7620) = +.6 (152) / -0
>300 (7620) = +.75 / -0
ALL OTHER DIMENSIONAL TOLERANCES:
X = ±.2 (5.08)
XX = ±.02 (5.1)
XXX = ±.005 (1.3)



APPROVALS	DATE
DRAWN BY R.CAWBICK	12/03/2001
CHECKED BY C.MCCORMICK	12/03/2001
APPROVED BY D.PARHAM	12/03/2001

L-com Global Connectivity		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY		D-SUBMINIATURE	
PRODUCT DESCRIPTION		SERIAL PORT ADAPTOR	
SIZE	PSCM NO.	DWG. NO.	REV.
B	43321	DMA010MF	A
SCALE: 2:1		CAD FILE: DMA010MF.SLDRAW	
		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[L-Com:](#)

[DMA010MF](#)