


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	04/21/2011	D.GRIFFIN
B	ECN 9306: ADDED CLIP TO CONNECTOR, NEW FORMAT	07/17/2018	D.FRISIELLO




PART NUMBER	LENGTH	
	METERS	FEET
FODBIFLC-01	1.0	[3.28]
FODBIFLC-02	2.0	[6.56]
FODBIFLC-03	3.0	[9.84]
FODBIFLC-05	5.0	[16.40]
FODBIFLC-10	10.0	[32.80]

NOTES:

- LC CONNECTOR ASSEMBLY POLISH TYPE: PC
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- PACKAGING:
INDIVIDUALLY PACKAGE EACH ASSEMBLY
IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ±.005 [1.3]	APPROVALS	DATE	 50 HIGH STREET NORTH ANDOVER, MA 01845		CATEGORY FIBER OPTICS	
	DRAWN BY D.CASTRO	04/06/2011				
	CHECKED BY D.PARHAM	04/15/2011	PRODUCT DESCRIPTION FLEX(LC-LC) BND IN 50μm DPX			
	APPROVED BY D.GALLAGHER	04/19/2011				
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321	DWG. NO. FODBIFLC	REV. B
	COLOR VARIATIONS MAY OCCUR		SCALE: NONE	CAD FILE: FODBIFLC.SLDDRW		SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[L-Com:](#)

[FODBIFLC-05](#) [FODBIFLC-01](#) [FODBIFLC-03](#) [FODBIFLC-02](#) [FODBIFLC-10](#)