


8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED TO PRODUCTION	8/18/00	R.CARRICK
B	ADDED LENGTHS TO CHART. CHANGED O.D TO 3.0MM SEE ECN #0792	11/29/00	R.CARRICK
C	REVISED CABLE MARKERS (ECN 1274)	01/02/03	MCCORMICK
D	ECN 6224: UPDATED DRAWING FORMAT & PACKAGING. ADDED ROHS STAMP	6/20/12	D. DESJARDIN



PART NUMBER	LENGTH	
	METERS	FEET
FODSTC-01	1.0	3.3
FODSTC-02	2.0	6.6
FODSTC-03	3.0	9.8
FODSTC-04	4.0	13.1
FODSTC-05	5.0	16.4
FODSTC-10	10.0	32.8
FODSTC-15	15.0	49.2
FODSTC-20	20.0	65.6
FODSTC-25	25.0	82.0
FODSTC-30	30.0	98.4
FODSTC-35	35.0	114.8
FODSTC-40	40.0	131.2
FODSTC-45	45.0	147.6
FODSTC-50	50.0	164.0
FODSTC-75	75.0	246.1
FODSTC-100	100.0	328.1
FODSTC-125	125.0	410.1
FODSTC-150	150.0	492.1



NOTES:

- CONNECTOR ASSEMBLY POLISH TYPE: PC
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPECIFICATION PS-0031.

RoHS Compliant

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: 012 [305] = +1 [25] / -0 >12 [305] 060 [1524] = +2 [51] / -0 >60 [1524] 0120 [3048] = +4 [102] / -0 >120 [3048] 0300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = N .2 .XX = N .02 .XXX = N .005	APPROVALS	DATE	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY RON CARRICK	8/16/2000		
	CHECKED BY ENG	8/16/2000	CATEGORY FIBER OPTICS	
	APPROVED BY AFC	8/18/2000	PRODUCT DESCRIPTION CA ST-ST 62.5/125 DUPLEX	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321
COLOR VARIATIONS MAY OCCUR		DWG. NO. FODSTC-01	REV. D	
SCALE: NONE		CAD FILE: FODSTC-01.SLDDRW	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[L-Com:](#)

[FODSTC-10](#) [FODSTC-30](#) [FODSTC-15](#) [FODSTC-20](#) [FODSTC-35](#) [FODSTC-04](#) [FODSTC-50](#) [FODSTC-150](#)
[FODSTC-01](#) [FODSTC-75](#) [FODSTC-03](#) [FODSTC-05](#) [FODSTC-100](#) [FODSTC-40](#) [FODSTC-25](#)