






THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/8/11	D.GRIFFIN



CAP NOT SHOWN IN THIS VIEW FOR CLARITY




RECOMMENDED
PANEL OPENING



NOTE:

1. HOUSING: ABS COLOR: BLACK
2. JACK IS CATEGORY 6 RATED
3. COMPLIANT TO MECHANICAL REQUIREMENTS OF TIA-1096.
4. ACCEPTS CONDUCTOR SIZES 24 TO 26 AWG
5. JACK IS INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
6. MAXIMUM PANEL THICKNESS: .060 [1.5]

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS	DATE	L-com Global Connectivity 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845			
	DRAWN BY D. PARHAM	02/03/2011				
	CHECKED BY D. CASTRO	02/04/2011	CATEGORY	TELECOM / MODULAR		
	APPROVED BY D. GALLAGHER	02/04/2011	PRODUCT DESCRIPTION			
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	JACK CAT6 RJ45/110			
			SIZE	FSCM NO.	DWG. NO.	REV.
			A	43321	MJS110C6-BLK	A
			SCALE: NONE	CAD FILE: MJS110C6-BLK.SLDDRW	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[L-Com:](#)

[MJS110C6-BLK](#)