

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC.. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 7101: DELETED WHT, GRN, LT GRY, YEL, CLEAR, PURP, PINK, ORG	10/10/13	D.FRISIELLO

D

D

C

C


B

B




A

A

.26
[6.6]




.54
[13.8]



CABLE ENTRY SIZE

CABLE ENTRY DIAMETER
SEE TABLE




ENTRY (DIA.)	mm	4.5	5.0	5.5	6.0	6.5
	INCHES	0.177	0.197	0.217	0.236	0.256
BLACK		MPC45D45-BLK	MPC45D50-BLK	MPC45D55-BLK	MPC45D60-BLK	MPC45D65-BLK
BLUE		MPC45D45-BLU	MPC45D50-BLU	MPC45D55-BLU	MPC45D60-BLU	MPC45D65-BLU
RED		MPC45D45-RED	MPC45D50-RED	MPC45D55-RED	MPC45D60-RED	MPC45D65-RED
DK GRAY		MPC45D45-DGRY	MPC45D50-DGRY	MPC45D55-DGRY	MPC45D60-DGRY	MPC45D65-DGRY



NOTES:

1. BOOTS ARE PACKAGED 50 PIECES PER BAG.
2. FLAMMABILITY RATING: UL94V-0

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: X = ± .2 XX = ± .02 .XXX = ±.005	APPROVALS		DATE		 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. PARHAM		01/12/2009		
	CHECKED BY M. MARTINEZ		01/13/2009		
	APPROVED BY D. GALLAGHER		01/13/2009		
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY				CATEGORY TELECOM/MODULAR
	COLOR VARIATIONS MAY OCCUR				PRODUCT DESCRIPTION LSZH SNAGLESS BOOT
	PROJECTION	SIZE A	FSCM NO. 43321	DWG. NO. MPC45D55	REV. E
		SCALE: NONE		CAD FILE: MPC45D55.SLDDRW	SHEET 1 OF 1

8 7 6 5 4 3 2 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[L-Com:](#)

[MPC45D60-RED](#) [MPC45D65-DGRY](#) [MPC45D65-BLK](#) [MPC45D60-DGRY](#) [MPC45D65-BLU](#) [MPC45D45-DGRY](#)
[MPC45D55-RED](#) [MPC45D45-BLU](#) [MPC45D60-BLK](#) [MPC45D65-RED](#) [MPC45D45-BLK](#) [MPC45D45-RED](#)
[MPC45D55-BLU](#) [MPC45D60-BLU](#) [MPC45D55-BLK](#)