


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/7/13	D.GRIFFIN
B	ECN 7107: ADDED JACKET TYPE TO CHART. CHANGED OM4 TO LSZH. UPD ROHS	10/17/13	D.FRISIELLO
C	ECN 9116: REVISED CHART SHEET 2	3/23/18	D.FRISIELLO




WIRING MAP	
"P1"	"P2"
1	1
2	2
3	3
4	4
5	5
6	6
7	7
8	8
9	9
10	10
11	11
12	12

NOTES:

- SEE SHEET 2 FOR PART NUMBERS, FIBER MODES, JACKET TYPES, COLORS, AND LENGTHS.
- MPO CONNECTOR MULTIMODE ASSEMBLY POLISH TYPE: UPC
MPO CONNECTOR SINGLE MODE ASSEMBLY POLISH TYPE: APC
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.13]	APPROVALS	DATE	L-com® Global Connectivity 50 HIGH STREET NORTH ANDOVER, MA 01845		
	DRAWN BY D.FRISIELLO	3/1/13			CATEGORY FIBER OPTICS PRODUCT DESCRIPTION 12-RIB MPO- M/M
	CHECKED BY D.GUTTADAURO	3/1/13			
	APPROVED BY D. GALLAGHER	3/1/13			
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY					
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. MPMM12	REV. C
		SCALE: NONE	CAD FILE: MPMM12.SLDDRW	SHEET 1 OF 2	

8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC.. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



CABLE CHART

MODEL NUMBER	LENGTH, MTR [FT]	CABLE MODE	JACKET TYPE	CABLE COLOR
MPMM12OM1-1	1.0 [3.28]	62.5/125 MULTIMODE OM1	OFNR (RISER) RATED	ORANGE
MPMM12OM1-3	3.0 [9.84]			
MPMM12OM1-5	5.0 [16.41]			
MPMM12OM1-10	10.0 [32.81]			
MPMM12OM1-25	25.0 [82.03]			
MPMM12OM1-50	50.0 [164.05]			
MPMM12OM1-100	100.0 [328.10]			
MPMM12OM2-1	1.0 [3.28]	50/125 MULTIMODE OM2	OFNR (RISER) RATED	ORANGE
MPMM12OM2-3	3.0 [9.84]			
MPMM12OM2-5	5.0 [16.41]			
MPMM12OM2-10	10.0 [32.81]			
MPMM12OM2-25	25.0 [82.03]			
MPMM12OM2-50	50.0 [164.05]			
MPMM12OM2-100	100.0 [328.10]			
MPMM12OM3-1	1.0 [3.28]	50/125 MULTIMODE OM3 LASER OPTIMIZED	OFNR (RISER) RATED	AQUA
MPMM12OM3-3	3.0 [9.84]			
MPMM12OM3-5	5.0 [16.41]			
MPMM12OM3-10	10.0 [32.81]			
MPMM12OM3-25	25.0 [82.03]			
MPMM12OM3-50	50.0 [164.05]			
MPMM12OM3-100	100.0 [328.10]			
MPMM12OM4-1	1.0 [3.28]	50/125 MULTIMODE OM4 LASER OPTIMIZED	LOW SMOKE ZERO HALOGEN	AQUA
MPMM12OM4-3	3.0 [9.84]			
MPMM12OM4-5	5.0 [16.41]			
MPMM12OM4-10	10.0 [32.81]			
MPMM12OM4-25	25.0 [82.03]			
MPMM12OM4-50	50.0 [164.05]			
MPMM12OM4-100	100.0 [328.10]			
MPMM12S-1	1.0 [3.28]	9/125 SINGLE MODE OS1	OFNR (RISER) RATED	YELLOW
MPMM12S-3	3.0 [9.84]			
MPMM12S-5	5.0 [16.41]			
MPMM12S-10	10.0 [32.81]			
MPMM12S-25	25.0 [82.03]			
MPMM12S-50	50.0 [164.05]			
MPMM12S-100	100.0 [328.10]			



50 HIGH STREET
NORTH ANDOVER, MA
01845

CATEGORY

FIBER OPTICS

PRODUCT DESCRIPTION

12-RIB MPO- M/M

SIZE
A

FSCM NO.
43321

DWG. NO.
MPMM12

REV.
C

SCALE: NONE

CAD FILE: MPMM12.SLDDRW

SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[L-Com:](#)

[MPMM12OM2-10](#)