



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	10/09/2018	BPUCHASKI



WIRING MAP



NOTES:

1. LENGTHS OVER 10 METERS (32.8 FT) ARE CHANNEL RATED.
2. PLENUM RATED JACKET MEETS OR EXCEEDS UL444 TYPE CMP AND FT6 REQUIREMENTS.
3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [5.1] .XXX = ±.005 [1.3] PROJECTION 	APPROVALS	DATE	 50 HIGH STREET NORTH ANDOVER, MA 01845
	DRAWN BY BPUCHASKI	10/08/2018	
	CHECKED BY JLABOY	10/08/2018	
	APPROVED BY DGUTTADAUR	10/08/2018	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY TELECOM/MODULAR
COLOR VARIATIONS MAY OCCUR			PRODUCT DESCRIPTION RJ45 CAT6A F/UTP 23SLD CMP
SIZE A	CAGE CODE 43321	DWG. NO. TRD695AP	REV. A
SCALE: NONE		CAD FILE: TRD695AP.SLDDRW	SHEET 1 OF 2

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC.. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

PART NUMBER	COLOR	LENGTH		PART NUMBER	COLOR	LENGTH		PART NUMBER	COLOR	LENGTH	
		FEET	METERS			FEET	METERS			FEET	METERS
TRD695APBLU-1	BLUE	1.0	0.30	TRD695APWHT-1	WHITE	1.0	0.30	TRD695APGRN-1	GREEN	1.0	0.30
TRD695APBLU-2	BLUE	2.0	0.61	TRD695APWHT-2	WHITE	2.0	0.61	TRD695APGRN-2	GREEN	2.0	0.61
TRD695APBLU-3	BLUE	3.0	0.91	TRD695APWHT-3	WHITE	3.0	0.91	TRD695APGRN-3	GREEN	3.0	0.91
TRD695APBLU-5	BLUE	5.0	1.52	TRD695APWHT-5	WHITE	5.0	1.52	TRD695APGRN-5	GREEN	5.0	1.52
TRD695APBLU-7	BLUE	7.0	2.13	TRD695APWHT-7	WHITE	7.0	2.13	TRD695APGRN-7	GREEN	7.0	2.13
TRD695APBLU-10	BLUE	10.0	3.05	TRD695APWHT-10	WHITE	10.0	3.05	TRD695APGRN-10	GREEN	10.0	3.05
TRD695APBLU-15	BLUE	15.0	4.57	TRD695APWHT-15	WHITE	15.0	4.57	TRD695APGRN-15	GREEN	15.0	4.57
TRD695APBLU-20	BLUE	20.0	6.10	TRD695APWHT-20	WHITE	20.0	6.10	TRD695APGRN-20	GREEN	20.0	6.10
TRD695APBLU-25	BLUE	25.0	7.62	TRD695APWHT-25	WHITE	25.0	7.62	TRD695APGRN-25	GREEN	25.0	7.62
TRD695APBLU-30	BLUE	30.0	9.14	TRD695APWHT-30	WHITE	30.0	9.14	TRD695APGRN-30	GREEN	30.0	9.14
TRD695APBLU-50	BLUE	50.0	15.24	TRD695APWHT-50	WHITE	50.0	15.24	TRD695APGRN-50	GREEN	50.0	15.24
TRD695APBLU-75	BLUE	75.0	22.86	TRD695APWHT-75	WHITE	75.0	22.86	TRD695APGRN-75	GREEN	75.0	22.86
TRD695APBLU-100	BLUE	100.0	30.48	TRD695APWHT-100	WHITE	100.0	30.48	TRD695APGRN-100	GREEN	100.0	30.48

		50 HIGH STREET NORTH ANDOVER, MA 01845	
CATEGORY			
TELECOM MODULAR			
PRODUCT DESCRIPTION			
RJ45 CAT6A F/UTP 23SLD CMP			
SIZE A	CAGE CODE 43321	DWG. NO. TRD695AP	REV. A
SCALE: NONE		CAD FILE: TRD695AP.SLDDRW	SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[infinite Electronics:](#)

[TRD695APGRN-2](#) [TRD695APGRN-1](#) [TRD695APWHT-2](#) [TRD695APWHT-75](#) [TRD695APBLU-50](#) [TRD695APGRN-25](#) [TRD695APBLU-2](#) [TRD695APGRN-30](#) [TRD695APBLU-15](#) [TRD695APGRN-5](#) [TRD695APWHT-15](#) [TRD695APWHT-20](#) [TRD695APBLU-10](#) [TRD695APGRN-7](#) [TRD695APGRN-100](#) [TRD695APBLU-75](#) [TRD695APWHT-100](#) [TRD695APWHT-7](#) [TRD695APBLU-25](#) [TRD695APGRN-50](#) [TRD695APBLU-20](#) [TRD695APGRN-10](#) [TRD695APBLU-5](#) [TRD695APWHT-10](#) [TRD695APBLU-3](#) [TRD695APBLU-1](#) [TRD695APGRN-20](#) [TRD695APWHT-25](#) [TRD695APWHT-50](#) [TRD695APGRN-15](#) [TRD695APWHT-30](#) [TRD695APBLU-100](#) [TRD695APBLU-7](#) [TRD695APGRN-75](#) [TRD695APWHT-1](#) [TRD695APBLU-30](#) [TRD695APGRN-3](#) [TRD695APWHT-3](#) [TRD695APWHT-5](#)