


8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC.. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	1/12/11	D.GRIFFIN
B	ECN 7015: REVISED L-COM LOGO, ROHS, FORMAT, ADDED CHANNEL NOTE	8/13/13	D.FRISIELLO
C	ECN 7274: REMOVED DRAIN WIRE FROM DESCRIPTION	1/31/14	D.FRISIELLO



NOTES:

MATERIAL:

PLUG HOUSING: POLYCARBONATE, CLEAR, UL94V-0
CONTACTS: PHOSPHOR BRONZE
CABLE JACKET: LOW SMOKE, ZERO HALOGEN, COLOR: SEE CHART
PLUG SHIELDING: BRASS
SNAGLESS BOOT: LOW SMOKE, ZERO HALOGEN, BLACK

FINISH:

CONTACTS: 50 μINCHES GOLD PLATED IN CONTACT AREA
OVER 100 μINCHES NICKEL PLATE OVERALL
PLUG SHIELDING: NICKEL PLATED

CABLE CHARACTERISTICS:

SHIELDED, FOUR TWISTED PAIR, CAT 6 MODULAR CABLE
CONDUCTORS: 26 AWG STRANDED BARE COPPER WITH ALUMINUM/ POLYESTER FOIL SHIELD AND TINNED COPPER BRAID SHIELD.


MISCELLANEOUS:


LENGTHS OVER 10 METERS (32.8 FT) ARE CHANNEL RATED.
PLUG CONFORMS TO TIA-1096.
CABLE ASSEMBLY TO BE TESTED FOR CONTINUITY.
CABLE ASSEMBLY TO BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

CE2011/65/EU(RoHS DIRECTIVE)

WIRING MAP



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: X = ± .2 [5.08] XX = ± .02 [5.1] XXX = ±.005 [1.3] PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		CATEGORY	TELECOM/MODULAR	PRODUCT DESCRIPTION CATEGORY 6 DBL SHIELDED LSZH PATCH CORD
	DRAWN BY D.FRISIELLO	4/26/11					
	CHECKED BY J.RUST	4/26/11					
	APPROVED BY D.GALLAGHER	4/26/11					
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		COLOR VARIATIONS MAY OCCUR		SIZE A		FSCM NO. 43321	
				SCALE: NONE	CAD FILE: TRD695DSZ.SLDDRW		SHEET 1 OF 2

MODEL NO.	LENGTH FEET [METERS]	COLOR
TRD695DSZ-BLK-1	1.0 [30]	BLACK
TRD695DSZ-BLK-2	2.0 [61]	BLACK
TRD695DSZ-BLK-3	3.0 [91]	BLACK
TRD695DSZ-BLK-5	5.0 [1.52]	BLACK
TRD695DSZ-BLK-7	7.0 [2.13]	BLACK
TRD695DSZ-BLK-10	10.0 [3.05]	BLACK
TRD695DSZ-BLK-15	15.0 [4.57]	BLACK
TRD695DSZ-BLK-20	20.0 [6.10]	BLACK
TRD695DSZ-BLK-25	25.0 [7.62]	BLACK
TRD695DSZ-BLK-30	30.0 [9.14]	BLACK
TRD695DSZ-BLK-40	40.0 [12.20]	BLACK
TRD695DSZ-BLK-50	50.0 [15.24]	BLACK
TRD695DSZ-BLK-60	60.0 [18.29]	BLACK
TRD695DSZ-BLK-75	75.0 [22.86]	BLACK
TRD695DSZ-BLK-80	80.0 [24.38]	BLACK
TRD695DSZ-BLK-90	90.0 [27.43]	BLACK
TRD695DSZ-BLK-100	100.0 [30.48]	BLACK
TRD695DSZ-GRY-1	1.0 [30]	GRAY
TRD695DSZ-GRY-2	2.0 [61]	GRAY
TRD695DSZ-GRY-3	3.0 [91]	GRAY
TRD695DSZ-GRY-5	5.0 [1.52]	GRAY
TRD695DSZ-GRY-7	7.0 [2.13]	GRAY
TRD695DSZ-GRY-10	10.0 [3.05]	GRAY
TRD695DSZ-GRY-15	15.0 [4.57]	GRAY
TRD695DSZ-GRY-20	20.0 [6.10]	GRAY
TRD695DSZ-GRY-25	25.0 [7.62]	GRAY
TRD695DSZ-GRY-30	30.0 [9.14]	GRAY
TRD695DSZ-GRY-40	40.0 [12.20]	GRAY
TRD695DSZ-GRY-50	50.0 [15.24]	GRAY
TRD695DSZ-GRY-60	60.0 [18.29]	GRAY
TRD695DSZ-GRY-75	75.0 [22.86]	GRAY
TRD695DSZ-GRY-80	80.0 [24.38]	GRAY
TRD695DSZ-GRY-90	90.0 [27.43]	GRAY
TRD695DSZ-GRY-100	100.0 [30.48]	GRAY

[illegible]

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY TELECOM/MODULAR			
PRODUCT DESCRIPTION CATEGORY 6 DBL SHIELDED LSZH PATCH CORD			
SIZE A	FSCM NO. 43321	DWG. NO. TRD695DSZ	REV. C
SCALE: NONE CAD FILE: TRD695DSZ.SLDDRW			SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[infinite Electronics:](#)

[TRD695DSZ-BLK-50](#) [TRD695DSZ-BLK-40](#) [TRD695DSZ-BLK-7](#) [TRD695DSZ-BLK-20](#) [TRD695DSZ-BLK-75](#)
[TRD695DSZ-BLK-25](#) [TRD695DSZ-BLK-3](#) [TRD695DSZ-BLK-30](#) [TRD695DSZ-BLK-1](#) [TRD695DSZ-BLK-100](#)
[TRD695DSZ-BLK-2](#) [TRD695DSZ-BLK-15](#) [TRD695DSZ-BLK-10](#) [TRD695DSZ-BLK-5](#) [TRD695DSZ-BLK-60](#)