


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	10/31/08	DFP



PART NUMBER	LENGTH		PART NUMBER	LENGTH	
	FEET	METERS		FEET	METERS
TRD815SPL-1	1.0	0.31	TRD815SPL-50	50.0	15.24
TRD815SPL-2	2.0	0.61	TRD815SPL-60	60.0	18.29
TRD815SPL-3	3.0	0.91	TRD815SPL-75	75.0	22.86
TRD815SPL-5	5.0	1.52	TRD815SPL-80	80.0	24.38
TRD815SPL-7	7.0	2.13	TRD815SPL-90	90.0	27.43
TRD815SPL-10	10.0	3.05	TRD815SPL-100	100.0	30.48
TRD815SPL-15	15.0	4.57	TRD815SPL-150	150.0	45.72
TRD815SPL-20	20.0	6.10	TRD815SPL-200	200.0	60.96
TRD815SPL-25	25.0	7.62	TRD815SPL-250	250.0	76.20
TRD815SPL-30	30.0	9.14	TRD815SPL-300	300.0	91.44
TRD815SPL-40	40.0	12.19			

NOTES

1. CABLE WIRED PER TIA/EIA 568B SEQUENCE.
2. PLUG SHIELDS ELECTRICALLY CONNECTED WITH THE DRAIN WIRE.
3. PLUGS CONFORM TO TIA-1096.
4. CABLES TESTED FOR CONTINUITY.
5. CABLES INDIVIDUALLY PACKAGED IN A POLYBAG.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .3 .XX = .15 PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY D. PARHAM	08/15/2008		
	CHECKED BY M. MARTINEZ	10/30/2008	CATEGORY MODULAR	
	APPROVED BY D. GALLAGHER	10/31/2008	PRODUCT DESCRIPTION CBL RJ45 CAT5E SHLD PLENUM	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321	DWG. NO. TRD815SPL
COLOR VARIATIONS MAY OCCUR		SCALE: NONE	CAD FILE: TRD815SPL.SLDDRW	REV. A
		SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[infinite Electronics:](#)

[TRD815SPL-60](#) [TRD815SPL-7](#) [TRD815SPL-10](#) [TRD815SPL-5](#) [TRD815SPL-3](#) [TRD815SPL-300](#) [TRD815SPL-150](#)
[TRD815SPL-15](#) [TRD815SPL-90](#) [TRD815SPL-250](#) [TRD815SPL-30](#) [TRD815SPL-40](#) [TRD815SPL-2](#) [TRD815SPL-](#)
[75](#) [TRD815SPL-80](#) [TRD815SPL-50](#) [TRD815SPL-20](#) [TRD815SPL-100](#) [TRD815SPL-25](#) [TRD815SPL-1](#)
[TRD815SPL-200](#)