


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	02/28/2018	DGUTTADAUR
B	ECN 9794:CBL JACKET CHANGED TO PVC,BLACK,OD WAS 5.8 MM,REM RoHS	04/24/2019	DGUTTADAUR



PART NUMBER	LENGTH	
	FEET	METERS
TRD855SRA6DBL-05M	1.64	0.5
TRD855SRA6DBL-1M	3.28	1.0
TRD855SRA6DBL-2M	6.56	2.0
TRD855SRA6DBL-3M	9.84	3.0
TRD855SRA6DBL-4M	13.12	4.0
TRD855SRA6DBL-5M	16.41	5.0
TRD855SRA6DBL-10M	32.82	10.0

NOTES:

1. PLUG CONFORMS TO TIA-1096
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [13]	APPROVALS	DATE
	DRAWN BY DCUI	02/03/2018
	CHECKED BY SLI	02/03/2018
	APPROVED BY SPAN	02/03/2018
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	
	COLOR VARIATIONS MAY OCCUR	

	50 HIGH STREET NORTH ANDOVER, MA 01845	
CATEGORY	TELECOM/MODULAR	
PRODUCT DESCRIPTION	C5e RJ45 S/UTP STR-LFT 26STR PVC HIFLX BLK	
SIZE A	FSCM NO. 43321	DWG. NO. TRD855SRA6DBL
SCALE: NONE	CAD FILE: TRD855SRA6DBL.SLDRW	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[L-Com:](#)

[TRD855SRA6DBL-2M](#) [TRD855SRA6DBL-05M](#) [TRD855SRA6DBL-3M](#) [TRD855SRA6DBL-4M](#) [TRD855SRA6DBL-5M](#)
[TRD855SRA6DBL-10M](#) [TRD855SRA6DBL-1M](#)