



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	1/3/13	D.GRIFFIN
B	ECN 7587: SHOWED LANYARD ON CABLE UPDATED ROHS	9/3/14	D. CASTRO



HIGH FLEX, CAT 5e SHIELDED TWISTED PAIR  
24AWG STRANDED TINNED COPPER WITH  
ALUM/POLY FOIL SHIELD AND TINNED  
COPPER BRAID.  
JACKET: THERMOPLASTIC ELASTOMER, BLACK



MODEL NUMBER	LENGTH METERS [FEET]
TRD8RG2-01	1.0 [3.28]
TRD8RG2-02	2.0 [6.56]
TRD8RG2-03	3.0 [9.84]
TRD8RG2-05	5.0 [16.41]
TRD8RG2-10	10.0 [32.81]

NOTES:

CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.

CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU(RoHS DIRECTIVE)



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ± .005 [13] PROJECTION 	APPROVALS DRAWN BY D.FRISIELLO CHECKED BY D.GUITTADAURO APPROVED BY D.GALLAGHER	DATE 11/28/12 11/28/12 11/28/12	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845 CATEGORY TELECOM/MODULAR PRODUCT DESCRIPTION IP68 RGRJ45 P/P ANOD TPE
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	
	SIZE <b>A</b>	FSCM NO. <b>43321</b>	
	SCALE: NONE	CAD FILE: TRD8RG2.SLDDRW	
SHEET 1 OF 1		REV. <b>B</b>	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[infinite Electronics:](#)

[TRD8RG2-02](#) [TRD8RG2-01](#) [TRD8RG2-03](#) [TRD8RG2-05](#) [TRD8RG2-10](#)