

8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



PART NUMBER	LENGTH	
	INCHES	MM
U2A00008-12I	12.0	[304.8]
U2A00008-24I	24.0	[609.6]
U2A00008-36I	36.0	[914.4]
U2A00008-72I	72.0	[1828.8]
U2A00008-120I	120.0	[3048.0]

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	06/28/17	J.LABOY



"P1"
USB SERIES "A" PLUG
UP EXIT
CONTACTS: 30 μINCHES
GOLD PLATING




.463
[11.75]
MIN.



"J1"
USB SERIES "A" RECEPTACLE
BULKHEAD ADAPTOR
CONTACTS: 30 μINCHES
GOLD PLATING


"P1" WIRING DIAGRAM

"J1"



- NOTES:
1. OPERATING TEMPERATURE: -10°C TO +70°C
 2. CABLE ASSEMBLY SHALL MEET USB 2.0 REQUIREMENTS.
 3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [13]	APPROVALS	DATE	 50 HIGH STREET NORTH ANDOVER, MA 01845		
	DRAWN BY S.LI	06/05/17			
	CHECKED BY B.ZHANG	06/05/17	CATEGORY	USB	
	APPROVED BY B.GATES	06/05/17	PRODUCT DESCRIPTION		
			USB2.0 A-F PNL MNT/90UP A-M SHLD		
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. U2A00008	REV. A
		SCALE: NONE		CAD FILE: U2A00008.SLDDRW	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[L-Com:](#)

[U2A00008-36I](#) [U2A00008-12I](#) [U2A00008-24I](#) [U2A00008-120I](#) [U2A00008-72I](#)