




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES UAD014MM-OD1	6/23/14	D. DESJARDIN



"P1"
SERIES "A"
USB PLUG



"P2"
SERIES "A"
USB PLUG



NOTES:

MATERIAL:

OVERMOLD: PVC, BEIGE
CONTACTS: BRASS
INSULATOR: PBT, UL94V-0, WHITE

FINISH:

SHELL: NICKEL SILVER
CONTACTS: GOLD OVER NICKEL

ELECTRICAL:

CURRENT RATING: 3 AMP
DIELECTRIC STRENGTH: 1000V AC FOR ONE MINUTE
INSULATOR RESISTANCE: 1000Ω MIN AT 500VDC

MISCELLANEOUS:

USB 2.0 COMPLIANT
ADAPTER SHALL BE TESTED FOR CONTINUITY.
ADAPTER SHALL BE INDIVIDUALLY PACKAGED IN
ACCORDANCE WITH L-COM SPEC. PS-0031.

REGULATORY COMPLIANCE:

CE2011/65/EU(RoHS DIRECTIVE)

WIRING MAP

"P1"	"P2"
PIN 1	PIN 1
PIN 2	PIN 2
PIN 3	PIN 3
PIN 4	PIN 4
SHELL	SHELL

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [5.1] .XXX = ±.005 [1.3] PROJECTION 	APPROVALS DRAWN BY C.MCCORMICK CHECKED BY D.PARHAM APPROVED BY R.CARRICK	DATE 12/20/02 12/20/02 12/20/02	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY USB	
	COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION ADPT, USB A-M/A-M	
	UAD014MM-OD1	SCALE: NONE	SIZE A	FSCM NO. 43321 DWG. NO. UAD014MM REV. A

CAD FILE: UAD014MM.SLDDRW

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[L-Com:](#)

[UAD014MM](#)