





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC.. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	07/11/17	J.YOU



PIN OUT

P1	P2
1	1
2	2
3	3
4	4
5	5
6	6
7	7
8	8
9	9
10	10
11	11
12	12
13	13
14	14
15	15
16	16
17	17
18	18
19	19
S	S

NOTES:

Electrical Properties:


1. It should be no any open/short, miswiring and intermittent failures.
2. The cable shall be 100% electrical test.
3. Voltage test: DC 300V 10MS;
Insulation resistance: 5.0M ohm/min;
Conducatace resistance: 5.0 ohm/max.

Machinery Character:

1. All dimension are "mm" except specified.
2. The cable should be clean, free of oiled/flash/burred.
3. Package: Individually packaged in a clear polybag.
4. Cable Ass'y shall be RoHS Compliant.

3	Outer molded: 45P PVC, Color: Black.	G	10
2	P2 Conn:HDMI 19pin,male,insulaton black,pin gold flash and shell gold flash.	PCS	1
1	P1 Conn:HDMI C type plug,Insulaton black,pin gold flash,shell gold flash.	PCS	1
Item	DESCRIPTION	UNIT	QTY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE	 50 HIGH STREET NORTH ANDOVER, MA 01845	
	DRAWN BY J.YOU	07/11/17		
	CHECKED BY B.GATES	07/11/17		
	APPROVED BY B.GATES	07/11/17		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.13]	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY AUDIO/VIDEO	
	COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION HDMI-AF TO HDM-CM	
	SIZE A	FSCM NO. 43321	DWG. NO. VHC00021	REV. A
	SCALE: NONE	CAD FILE: VHC00021.SLDDRW		SHEET 1 OF 1



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[L-Com:](#)

[VHC00021](#)