




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	07/07/17	J.YOU



PIN OUT

P1	P2	P1	P2
1	1	14	14
2	2	15	15
3	3	16	16
4	4	17	17
5	5	18	18
6	6	19	19
7	7	20	20
8	8	21	21
9	9	22	22
10	10	23	23
11	11	24	24
12	12	S	S
13	13		

NOTES

Electrical Properties:

- It should be no any open/short, miswiring and intermittent failures.
- The cable shall be 100% electrical test.
- Voltage test: DC 300V 10MS;
Insulation resistance: 5.0M ohm/min;
Conductance resistance: 5.0 ohm/max.

Machinery Character:

- All dimension are "mm" except specified.
- The cable should be clean, free of oiled/flash/burred.
- Package: Individually packaged in a clear polybag.
- Cable Ass'y shall be RoHS Compliant.

Item	DESCRIPTION	UNIT	QT'Y
4	Outer molded: 45P PVC, Color: Black.	G	10
3	Screw: 3.0*37.0MM(#4-40UNC), nickel plated.	PCS	2
2	P2 Conn:DVI(24+5)pin, female, with front screw, insulaton black, shell & pin gold flash.	PCS	1
1	P1Conn:DVI (24+5)pin, male, insulaton black, shell & pin gold flash.	PCS	1

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] DIMENTIONAL TOLERANCES: .X ± 1 [2.54] .XX ± 0.1 [.25] .XXX ± 0.05 [.13] ANGULAR TOLERANCES: ANGLES: ±1° PROJECTION 	APPROVALS	DATE	 	
	DRAWN BY J.YOU	07/07/17		
	CHECKED BY B.GATES	07/07/17	CATEGORY AUDIO/VIDEO	
	APPROVED BY B.GATES	07/07/17	PRODUCT DESCRIPTION DVI 24+5 M TO DVI F RA ADPT	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			SIZE A	FSCM NO. 43321
COLOR VARIATIONS MAY OCCUR			DWG. NO. VIC00006	REV. A
SCALE: NONE			CAD FILE: VIC00006.SLDDRW	
			SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[L-Com:](#)

[VIC00006](#)