






THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
E	ECN 12067: REVISED NOTES, ADDED NOTE 5 (TORQUE), REVISED FORMAT	09/02/2022	GUTTADURO




NOTES:

1. THESE CABLE ASSEMBLIES ARE CONSTRUCTED TO MEET THE REQUIREMENTS OF THE UNIVERSAL SERIES BUS SPECIFICATION USB 2.0
2. CONNECTOR CONTACTS HAVE 30 MICROINCHES GOLD PLATING OVER NICKEL PLATING.
3. INGRESS PROTECTION RATING IS IP67 (J1 ONLY, MATED)
4. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
5. SUGGESTED MAX. TORQUE VALUE FOR HEX NUT IS 1.5N-m (13.2 lbf-in)
6. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPEC. PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS	DATE
OVERALL CABLE LENGTH	12 [305] +1/-0	DRAWN BY	02/01/2010
>12 [305] <40 [1020]	+1 [25] /-0	CHECKED BY	02/01/2010
>40 [1020] <120 [3048]	+4 [102] /-0	APPROVED BY	02/01/2010
>120 [3048] <300 [7620]	+6 [152] /-0		
>300 [7620] <1000 [25400]	+10 [254] /-0		
ALL OTHER DIMENSIONAL TOLERANCES:	X = ± 2 [5] XX = ± 0.02 [0.5] XXX = ± .005 [1.3]	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION
	FRACTIONS ± 1/32 ANGLES ± 1°		CA IP67 USBA-F/A-M SHLD
THIRD-ANGLE PROJECTION	COLOR VARIATIONS MAY OCCUR	SIZE	CAGE CODE
		B	43321
			WPUSBAXSH
	SCALE: NONE	CAD FILE: WPUSBAXSH.SLDRW	REV. E
			SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[L-Com](#):

[WPUSBAXSH-3M](#) [WPUSBAXSH-05M](#) [WPUSBAXSH-5M](#) [WPUSBAXSH-1M](#) [WPUSBAXSH-2M](#)