

120-108 • 120-132
Standard and Ultra Small Diameter
PEEK Helical Convoluted Tubing
for Fiber Optic Applications



Standard diameter low-smoke, zero-halogen tubing with outstanding crush resistance



How To Order

Product Series

Basic No.

Dash No.
(Table I)

120

- 108

- 16

B

B = PEEK/Color Black
P = PEEK/Color Purple
R = PEEK/Color Red
(Omit for Natural)




Table I				
Tubing Size	Fractional Size Ref	A Inside Dia		B Dia Max
		Min	Nom	
06	3/16	.181 (4.6)	.187 (4.7)	.307 (7.8)
09	9/32	.273 (6.9)	.281 (7.1)	.405 (1.3)
10	5/16	.300 (7.6)	.312 (7.9)	.440 (11.2)
12	3/8	.364 (9.2)	.375 (9.5)	.500 (12.7)
16	1/2	.485 (12.3)	.500 (12.7)	.630 (16.0)
20	5/8	.608 (15.4)	.625 (15.9)	.750 (19.1)
24	3/4	.730 (18.5)	.750 (19.1)	.890 (22.6)

Table I (continued)				
Tubing Size	Fractional Size Ref	A Inside Dia		B Dia Max
		Min	Nom	
28	7/8	.855 (21.7)	.875 (22.2)	1.060 (26.9)
32	1	.980 (24.9)	1.000 (25.4)	1.195 (3.4)
40	1 1/4	1.220 (31.0)	1.250 (31.8)	1.500 (38.1)
48	1 1/2	1.480 (37.6)	1.500 (38.1)	1.780 (45.2)
56*	1 3/4	1.735 (44.1)	1.750 (44.5)	2.020 (51.3)
64*	2	1.980 (5.3)	2.000 (5.8)	2.280 (57.9)

Packaging / Notes

- Unless otherwise specified, Conduit will be shipped per standard package. Length to be as follows: 3/16 to 3/4 I.D.; 80 ft. min. 1 to 2 I.D.; 40 ft. min.

* Consult factory for availability

Special purpose, ultra-small diameter, low-smoke, zero-halogen tubing with outstanding crush resistance for fiber optic applications (one size only)



How To Order

Product Series


Basic No.

120

- 132

B

B = PEEK/Color Black
P = PEEK/Color Purple
R = PEEK/Color Red
(Omit for Natural)



Packaging / Notes

- Unless otherwise specified, Conduit will be shipped per standard package. Minimum length supplied will be 10 feet (3 m), with a maximum length of four lengths per package.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[120-132](#) [120-108-03](#) [120-108-06P](#) [120-108-09P](#) [120-108-10P](#) [120-108-12P](#) [120-108-12R](#) [120-108-14P](#) [120-108-16P](#) [120-108-20P](#) [120-108-24P](#) [120-108-28P](#) [120-108-32P](#) [120-108-64R](#) [120-132P](#)