



RJ45 AND USB 2.0

Contacts, Tools, and Accessories




370-001 Cable Sealing Backshell with Rotatable Coupling for 38999 Series III Type Connectors


MIL-DTL-38999 Type

How To Order									
Sample Part Number	370	H	S	001	M	17	03	D	1.5
Series/Basic Part No.	370 - low Profile								
Connector Designator	H = 38999								
Angular Function	A = 90° B = 45° S = Straight								
Basic Part No.	001								
Finish	See Material and Finish Table								
Shell Size	15, 17, 19								
Dash No.	See Dash Number Table								
Strain Relief Style	D = Nut								
Length	1/2 inch increments (e.g. 6 = 3 inches); Straight only Minimum Order Length 1.5 Inch (See Note 1)								


Straight (S)




45° (B)



90° (A)



STRAIN RELIEF STYLE D



Dimensions						
Shell Size	A Thread	C Typ.	E Max	F Max	G Max	H Max
15	M22 X 1 -- 6H	1.07 (27.2)	.645 (16.4)	2.359 (59.9)	.700 (17.8)	2.369 (60.2)
17	M25 X 1 -- 6H	1.21 (30.7)	.738 (18.7)	2.469 (62.7)	.885 (22.5)	2.459 (62.5)
19	M28 X 1 -- 6H	1.36 (34.5)	.926 (23.5)	2.659 (67.5)	.975 (24.8)	2.629 (66.8)

Materials and Finishes ¹	
NF	Aluminum/Cadmium, olive drab
ME	Aluminum/Electroless nickel
MT	Aluminum/ Nickel PTFE
ZR	Aluminum/ Black zinc-nickel

Dash Number			
Dash No.	Z Max	Cable Range	
		Min	Max
03	.630 (16.0)	.156 (4.0)	.250 (6.4)
04	.755 (19.2)	.188 (4.8)	.312 (7.9)
06	.942 (23.9)	.281 (7.1)	.438 (11.1)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[370HS001NF1516H4](#) [370HS001NF2110H4](#) [370HS001NF2116H4](#) [370HS001M2306A8C](#) [370HA001M0904A](#)
[370HA001M1306A](#) [370HS001M1306A3](#) [370HS001M1504A4](#) [370HS001M1510A3](#) [370HS001N1310H4](#)
[370HS001C1910D4C](#) [370HS001C1912D4C](#) [370HS001NF1108A3-445](#) [370HA001NF2516H](#) [370HS001NF2524M5](#)
[370HS001M1306H4-204](#) [370HS001M1712H4-204](#) [370HA001NF1108A-445](#) [370HS001M2516H4-204](#)
[370HB001NF2516H-98J](#) [370HS001M2312H4-204](#) [370HS001M1306A4](#)