





600L005
LN29729 (SJT)
Plug and Receptacle Holder



RECEPTACLE HOLDER



PLUG HOLDER

Shell Size	Max. Recommended Torque (Inch Pounds)	A Dia. Max.	B Dia. Max.	C Dim. Max.
08	40	.478 (12.1)	.358 (9.1)	.910 (23.1)
10	40	.599 (15.2)	.486 (12.3)	.910 (23.1)
12	40	.758 (19.3)	.603 (15.3)	.910 (23.1)
14	40	.882 (22.4)	.728 (18.5)	.910 (23.1)
16	40	1.007 (25.6)	.853 (21.7)	.910 (23.1)
18	40	1.133 (28.8)	.958 (24.3)	.910 (23.1)
20	80	1.257 (31.9)	1.083 (27.5)	.910 (23.1)
22	80	1.382 (35.1)	1.208 (30.7)	.910 (23.1)
24	80	1.507 (38.3)	1.333 (33.9)	.910 (23.1)

APPLICATION NOTES

1. Metric dimensions (mm) are indicated in parentheses.
2. Material: Case hardened carbon steel with electroless nickel finish.
3. Receptacle and plug holder drives: 1/4" - Shell sizes 08, 10, 12; 3/8" - Shell sizes 14 and up.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

<u>600L005-24P</u>	<u>600L005-14P</u>	<u>600L005-22R</u>	<u>600L005-10P</u>	<u>600L005-16P</u>	<u>600L005-12R</u>	<u>600L005-24R</u>	<u>600L005-18P</u>
<u>600L005-14R</u>	<u>600L005-08P</u>	<u>600L005-10R</u>	<u>600L005-20P</u>	<u>600L005-16R</u>	<u>600L005-22P</u>	<u>600L005-08R</u>	<u>600L005-18R</u>
<u>600L005-12P</u>	<u>600L005-20R</u>						