



710-077
Metal Multi-Branch Transitions
for Series 72 & 74 Tubing and Series 75 Conduit



Metal Multi-Branch Transitions for use with Transition Fittings



How To Order



E

Table III: Conduit Dash No./Dimensions

Dash No.	Conduit Size (Ref)			H Thread Class 2A	D Max	E Max
	72	74	75			
06	06	06	-	7/16 - 28 UNEF	1.97 (50.0)	1.20 (30.5)
08	-	-	08	1/2 - 20 UNF	1.97 (50.0)	1.20 (30.5)
09	09	09	09	9/16 - 24 UNEF	2.13 (54.1)	1.30 (33.0)
10	-	10	-	9/16 - 24 UNEF	2.13 (54.1)	1.30 (33.0)
12	12	12	12	5/8 - 24 UNEF	2.22 (56.4)	1.34 (34.0)
14	14	14	-	11/16 - 24 UNEF	2.37 (60.2)	1.49 (37.8)
16	16	16	16	3/4 - 20 UNEF	2.37 (60.2)	1.49 (37.8)
20	20	20	20	7/8 - 20 UNEF	2.69 (68.3)	1.70 (43.2)
24	24	24	24	1 - 20 UNEF	2.75 (69.9)	1.84 (46.7)
28	28	28	-	1 3/16 - 18 UNEF	3.06 (77.7)	2.09 (53.1)
32	32	32	32	1 5/16 - 18 UNEF	3.28 (83.3)	2.23 (56.6)
40	40	40	40	1 1/2 - 18 UNEF	3.59 (91.2)	2.50 (63.5)
48	48	48	48	1 3/4 - 18 UNS	4.23 (107.4)	2.96 (75.2)
56	-	56	56	2 - 18 UNS	5.00 (127.0)	3.50 (88.9)
64	-	64	64	2 1/4 - 16 UN	5.00 (127.0)	3.50 (88.9)
80	-	-	80	2 3/4 - 16 UN	5.70 (144.8)	4.10 (104.1)

* Consult factory for adapters using 3.000 inch (76.2) conduit

Table II: Finish

Sym	Finish
B	Olive Drab over Cadmium Plate
J	Gold Iridite over Cadmium Plate over Nickel
M	Electroless Nickel
N	Olive Drab over Cadmium Plate over Nickel
NC	Zinc Cobalt, Olive Drab
NF	Olive Drab over Cadmium Plate over Electroless Nickel (1000 Hour salt Spray)
T	Bright Dip Cadmium over Nickel
Z1	Passivate

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[710-077NFA20B16C16D16B](#) [710-077MA40B24C24D24A](#) [710-077MA24B24C24D24A](#) [710-077NFA40B28C20D16A](#)
[710-077MA32B24C24D24A](#) [710-077NFA32B24C16D16A](#)