

790-045P


Crimp Terminated Cable Receptacle Connector with Integrated Banding Porch, Pin Contacts

How To Order



790-045P Cable Receptacles

CRIMP PIN CONTACTS, INTEGRATED BANDING PORCH



Rugged, lightweight 790-045P connectors feature machined aluminum shells, fluorosilicone face seals and wire grommets for environmental protection. Contacts are rear-release snap-in crimp. Connectors are supplied with crimp contacts packaged separately. Size #23 signal pins accept up to #22 AWG wire. Size #16 contacts accept #16-18 AWG wire. Size #12 contacts accept #12-14 AWG wire. Size 12 and 16 cavities also accept coaxial contacts purchased separately. Connector shell features an integrated banding porch for attachment of EMI shielding.

HOW TO ORDER			
Sample Part Number			
790-045P	H-10P4	M	B
Base Part Number	Shell Size - Insert Arrangements	Shell Finish	Mounting Hardware
790-045P Cable Receptacle with Crimp Pin Contacts and Integrated Banding Porch	See Table 1 for Available Insert Arrangements. To order a connector without size #16 or #12 power pins, substitute "W" instead of "P" in the insert arrangement. Example: 36P2 is supplied with 2 power pins. 36W2 is supplied less the power pins. See Section B for coaxial contacts purchased separately.	M Electroless Nickel <i>general purpose applications</i> MT Nickel-PTFE 1000 Hour Grey™ <i>maximum corrosion protection and durability (non-reflective grey)</i> ZNU Zinc-Nickel with Black Chromate <i>tactical applications (non-reflective black)</i> Additional shell finishes are listed on page C-9.	B Thru-Hole, No Hardware M Low-profile captivated jackscrew, hex socket, jacking MF Low-profile captivated jackscrew, hex socket, floating S Low-profile captivated Jackscrew, slotted, jacking SF Low-profile captivated Jackscrew, slotted, floating P Jackpost, female, with nut and split washer

SPECIFICATIONS	
Current Rating	#23 5 AMPS, #16 13 A., #12 23 A.
Dielectric Withstanding Voltage	#23 500 VAC RMS, #12 and #16 1800 VAC RMS
Insulation Resistance	5000 megohms minimum
Operating Temperature	-65° C. to +150° C.
Shock	300 g.
Vibration	37 g.

MATERIALS AND FINISHES	
Shell	Aluminum alloy
Contacts	Copper alloy, 50 microinches gold plated
Insulators	Liquid crystal polymer (LCP)
Retention Clips	Beryllium copper alloy
Interfacial Seal, Grommet	Flourosilicone rubber
Hardware	300 series stainless steel

Dimensions in Inches (millimeters) are subject to change without notice.

790-045P


Crimp Terminated Cable Receptacle Connector with Integrated Banding Porch, Pin Contacts

Dimensions


Table Contact Arrangements

Layout	Contact Quantity		Face View
#23#16#12			
A-5	5		
B-2P2	2		
B-9	9		
C-13	13		
D-15	15		
D-3P3	3		
D-7P2	5	2	
E-11P2	9	2	
E-19	19		
E-7P3	4	3	
F-15P2	13	2	
F-23	23		
F-5P5	5		
G-33	33		
H-10P4	6	4	
H-29P7	22	7	
H-36P2	34	2	
H-54P2	52	2	
H-5P5		5	
H-66	66		
J-17P4	13	4	
J-25P2	23	2	
J-33	33		
J-7P7	7		
K-27P4	23	4	
K-35P2	33	2	
K-43	43		
K-9P9	9		
L-6P6		6	
L-78	78		
M-102	102		

CROSS-SECTIONAL VIEW OF 790-045P



790-045P Dimensions

SHELL SIZES A, B, C, D,
E, F, G, J, K

SHELL SIZES H, L

790-045P DIMENSIONS

Shell Size	A Max.		B Basic		C Max.		D Max.		E Max.		F Max.	
	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.
A	.785	19.94	.565	14.35	.400	10.16	.308	7.82	.440	11.18	.360	9.14
B	.935	23.75	.715	18.16	.551	14.00	.308	7.82	.590	14.99	.370	9.40
C	1.085	27.56	.865	21.97	.701	17.81	.308	7.82	.740	18.80	.390	9.91
D	1.185	30.10	.965	24.51	.801	20.35	.308	7.82	.840	21.34	.400	10.16
E	1.335	33.91	1.115	28.32	.951	24.16	.308	7.82	.990	25.15	.400	10.16
F	1.485	37.72	1.265	32.13	1.101	27.97	.308	7.82	1.140	28.96	.410	10.41
G	1.435	36.45	1.215	30.86	1.079	27.41	.395	10.03	1.130	28.70	.490	12.45
H	2.175	55.25	1.800	45.72	1.450	36.83	.410	10.41	1.525	38.74	.510	12.95
J	1.845	46.86	1.615	41.02	1.460	37.08	.308	7.82	1.490	37.85	.410	10.41
K	2.240	56.90	2.015	51.18	1.860	47.24	.308	7.82	1.890	48.01	.430	10.92
L	2.420	61.47	2.036	51.71	1.686	42.82	.410	10.41	1.760	44.70	.520	13.21
M	2.575	65.41	1.675	42.55	1.675	42.55	.470	11.94	1.850	46.99	.615	15.62

Dimensions in Inches (millimeters) are subject to change without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[790-045PD-15MM](#) [790-045PB-9MTB](#) [790-045PG-33MM](#) [790-045PK-9P9MM](#) [790-045PF-23MTB](#) [790-045PH-36W2MB](#) [790-045PD-15MS](#) [790-045PL-78MS](#) [790-045PJ-33MM](#) [790-045PL-6P6MM](#) [790-045PH-66MB](#) [790-045PE-19MM](#) [790-045PG-33MTB](#) [790-045PA-5MMF](#) [790-045PA-5MTM](#) [790-045PB-2P2MB](#) [790-045PB-2P2MMF](#) [790-045PB-2P2MTMF](#) [790-045PB-9MB](#) [790-045PB-9MS](#) [790-045PB-9MTM](#) [790-045PB-9MTSF](#) [790-045PC-13MB](#) [790-045PD-15MMF](#) [790-045PD-15MP](#) [790-045PD-3P3MMF](#) [790-045PD-7P2MMF](#) [790-045PE-11P2MMF](#) [790-045PE-19MMF](#) [790-045PE-19MS](#) [790-045PE-19MTMF](#) [790-045PE-19MTSF](#) [790-045PF-23MMF](#) [790-045PF-23MS](#) [790-045PF-23MTM](#) [790-045PF-5P5MB](#) [790-045PF-5P5MS](#) [790-045PG-33MB](#) [790-045PG-33MP](#) [790-045PG-33MTSF](#) [790-045PH-10P4MB](#) [790-045PH-29P7MMF](#) [790-045PH-5W5MB](#) [790-045PH-5W5MMF](#) [790-045PH-5W5MP](#) [790-045PH-66MM](#) [790-045PH-66MP](#) [790-045PH-66Z1M](#) [790-045PH-66Z1S](#) [790-045PJ-33MMF](#) [790-045PJ-7P7MM](#) [790-045PK-43MMF](#) [790-045PK-43MS](#) [790-045PK-9P9MS](#) [790-045PL-78MB](#) [790-045PL-78MP](#) [790-045PM-102MMF](#) [790-045PM-102MS](#) [790-045PM-102MTMF](#) [790-045PA-5MB](#) [790-045PL-78MM](#)