



TABLE I				STANDARD SHIPPING PACKAGE/3				REVISIONS			
DASH NO	A INSIDE DIA		B OUTSIDE DIA		DASH NO	MAX LENGTH PER PKG		SYM.	DESCRIPTION	DATE	APPROVED
	MIN	MAX	MIN	MAX		09 & 12	200 FT (60 m)				
09	.24 (6.1)	.28 (7.1)	.38 (9.7)	.42 (10.7)	16 THRU 52	100 FT (30 m)		A	RELEASED	03/19/02	DM.
12	.33 (8.4)	.37 (9.4)	.48 (12.2)	.52 (13.2)				B	REVISED PER DCN #20075	11/12/02	DM.
16	.45 (11.4)	.50 (12.7)	.60 (15.2)	.66 (16.8)				C	REVISED PER DCN #20210	12/17/02	KB
20	.57 (14.5)	.62 (15.7)	.71 (18.0)	.77 (20.0)				D	REVISED PER DCN #22208	03/30/04	R.P.
24	.69 (17.5)	.75 (19.1)	.88 (22.4)	.94 (23.9)				E	REVISED PER DCN #36954	10/15/10	ACM
28	.81 (20.6)	.87 (22.1)	1.00 (25.4)	1.08 (27.4)				F	REVISED PER DCN #38793	05/05/11	ACM
32	.93 (23.6)	1.00 (25.4)	1.12 (28.4)	1.20 (30.5)							
40	1.18 (30.0)	1.25 (31.8)	1.36 (34.5)	1.44 (36.6)							
48	1.43 (36.3)	1.50 (38.1)	1.63 (41.4)	1.71 (43.4)							
52	1.56 (39.6)	1.63 (41.4)	1.77 (45.0)	1.85 (47.0)							

PART NUMBER DEVELOPMENT



NOTES:

- IDENTIFY WITH MANUFACTURERS NAME AND P/N, SPACE PERMITTING.
- METRIC DIMENSIONS (IN PARENTHESES) ARE GIVEN FOR REFERENCE ONLY, AND ARE BASED UPON 1 INCH = 25.4 mm.
- UNLESS OTHERWISE SPECIFIED, CONDUIT WILL BE SHIPPED PER STANDARD PACKAGE MIN LENGTH SUPPLIED WILL BE 10 FEET (3m) WITH A MAX OF 4 LENGTH PER PKG.
- CONSULT FACTORY FOR SIZES NOT SHOWN.
- MATERIAL/FINISH:
CONVOLUTED TUBING - KYNAR NOT THERMALLY STABILIZED.

THIS COPYRIGHTED DOCUMENT IS THE PROPERTY OF GLENNAIR, INC. AND IS FURNISHED ON THE CONDITION THAT IT IS NOT TO BE DISCLOSED, REPRODUCED IN WHOLE OR IN PART, OR USED TO SOLICIT QUOTATIONS FROM COMPETITIVE SOURCES, OR USED FOR MANUFACTURE BY ANYONE OTHER THAN GLENNAIR, INC. WITHOUT WRITTEN PERMISSION FROM GLENNAIR, INC. THE INFORMATION HEREIN HAS BEEN DEVELOPED AT GLENNAIR'S EXPENSE AND MAY BE USED FOR ENGINEERING EVALUATION AND INCORPORATION INTO TECHNICAL SPECIFICATIONS AND OTHER DOCUMENTS WHICH SPECIFY PROCUREMENT OF PRODUCTS FROM GLENNAIR, INC.	
UNLESS OTHERWISE SPECIFIED	
DRAWN	D. MONTOYA 03/19/02
CHECK	K. BAILEY 03/19/02
ENGR	M. P. 03/19/02
DIMENSIONS ARE IN INCHES	
TOLERANCES:	
FRACTIONS	± 1/16
DECIMALS	± .XX .03
ANGLES	± .XXX .015
DO NOT SCALE THIS DRAWING	P/C 12
B/F 02-1349	
GLENNAIR, INC. 1211 AIR WAY - GLENDALE - CALIFORNIA 91201	
TUBING, CONVOLUTED, ANNULAR	
CODE IDENT. NO. SIZE	REV.
06324 C 120-125	F
SCALE N/A	WEIGHT N/A
SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[120-125-09](#) [120-125-12](#) [120-125-12BL](#) [120-125-12R](#) [120-125-12Y](#) [120-125-16](#) [120-125-16R](#) [120-125-16Y](#) [120-125-20](#) [120-125-20R](#) [120-125-20Y](#) [120-125-24](#) [120-125-24R](#) [120-125-24Y](#) [120-125-28](#) [120-125-28R](#) [120-125-28Y](#)
[120-125-32](#) [120-125-32R](#) [120-125-40](#) [120-125-52BL](#) [120-125-56](#) [120-125-09BL](#) [120-125-48BL](#)