



D38999/41

Box Mount Hermetic Receptacle

MIL-DTL-38999 Series IV

How To Order: MS

B





TABLE II: CONTACT SIZE	
PRINTED CIRCUIT TAIL CONFIGURATIONS CONTACT STYLE C AND D	
SIZE 12 AND SIZE 16	
SIZE 22D AND SIZE 20	
Contact Size	ø P
22D	.011 (0.28) .015 (0.38)
20	.024 (0.61) .028 (0.71)
16	.0635 (1.61) .0615 (1.56)
12	.095 (2.41) .093 (2.36)

WIRE ACCOMODATION	
Contact Size	Wire Guage
22D	#22 - #28
20	#20 - #24
16	#16 - #20
12	#12 - #14



234-100-H2
Box Mount Hermetic Receptacle
MIL-DTL-38999 Series IV Type



How To Order: Commercial

Connector Series 230-010 - Series IV Type	Shell Style H2 - Hermetic Box Mount Receptacle	Shell Size 11, 13, 15, 17, 19, 21, 23, 25	Contact Termination P - Pin, Solder Cup S - Socket, Solder Cup X - Pin, Eyelet Z - Socket, Eyelet C - Pin, PCB D - Socket, PCB
234	- 100	- H2	Z1
	11	- 35	P
		N	
Connector Type 100 - Hermetic Receptacle	Connector Material / Finish ZL - CRES, Nickel Z1 - CRES, Passivated	Insert Arrangement Per MIL-STD-1560; See Pages B-2 - B-4	Alternate Key Position A, B, C, D, K, L, M, R, U (N = Normal)

B

HERMETIC LEAK RATE MOD CODES	
Designator	Required Leak Rate
-585A	1 x 10 ⁻¹⁰ cc Helium per second
-585B	1 x 10 ⁻⁹ cc Helium per second
-585C	1 x 10 ⁻⁸ cc Helium per second




TABLE I: CONNECTOR DIMENSIONS

SHELL SIZE CODE	SHELL SIZE	A SQ	B BSC	C DIA	D DIA	øG HOLES ±.005(0.1)	øH MIN	øJ MIN	K ±.005(0.1)
B	11	1.051(26.7) 1.008(25.6)	.812(20.6)	.793(20.1) .778(19.8)	.138(3.5) .122(3.1)	.128(3.3)	.781(19.8)	.625(15.9)	.812(20.6)
C	13	1.145(29.1) 1.102(28.0)	.906(23.0)	.919(23.3) .904(23.0)	.138(3.5) .122(3.1)	.128(3.3)	.921(23.4)	.750(19.1)	.906(23.0)
D	15	1.240(31.5) 1.197(30.4)	.969(24.6)	1.044(26.5) 1.029(26.1)	.138(3.5) .122(3.1)	.128(3.3)	1.047(26.6)	.906(23.0)	.968(24.6)
E	17	1.334(33.9) 1.291(32.8)	1.062(27.0)	1.170(29.7) 1.155(29.3)	.138(3.5) .122(3.1)	.128(3.3)	1.218(30.9)	1.016(25.8)	1.062(27.0)
F	19	1.460(37.1) 1.417(36.0)	1.156(29.4)	1.294(32.9) 1.279(32.5)	.138(3.5) .122(3.1)	.128(3.3)	1.296(32.9)	1.142(29.0)	1.156(29.4)
G	21	1.583(40.2) 1.539(39.1)	1.250(31.8)	1.419(36.0) 1.404(35.7)	.138(3.5) .122(3.1)	.128(3.3)	1.421(36.1)	1.266(32.2)	1.250(31.8)
H	23	1.709(43.4) 1.665(42.3)	1.375(34.9)	1.544(39.2) 1.529(38.8)	.157(4.0) .142(3.6)	.154(3.9)	1.546(39.3)	1.375(34.9)	1.375(34.9)
J	25	1.835(46.6) 1.791(45.5)	1.500(38.1)	1.670(42.4) 1.654(42.0)	.157(4.0) .142(3.6)	.154(3.9)	1.672(42.5)	1.484(37.7)	1.500(38.1)

Dimensions in Inches (millimeters) are subject to change without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[234-100-H2Z111-05PN](#) [234-100-H2ZL11-05PN](#) [234-100-H2ZL11-05XN](#) [234-100-H5ZL11-05PN](#) [234-100-H5ZL17-08PN](#) [D38999/41YG39DA](#) [D38999/41YG39DB](#) [D38999/41YG39DC](#) [D38999/41YG39DD](#) [D38999/41YG39DK](#)
[D38999/41YG39DN](#) [D38999/41YG39SA](#) [D38999/41YG39SB](#) [D38999/41YG39SC](#) [D38999/41YG39SD](#)
[D38999/41YG39SK](#) [D38999/41YG39SN](#) [D38999/41YG39ZA](#) [D38999/41YG39ZB](#) [D38999/41YG39ZC](#)
[D38999/41YG39ZD](#) [D38999/41YG39ZK](#) [D38999/41YG39ZN](#) [D38999/41YH53DA](#) [D38999/41YH53DB](#)
[D38999/41YH53DC](#) [D38999/41YH53DD](#) [D38999/41YH53DK](#) [D38999/41YH53DN](#) [D38999/41YH53SA](#)
[D38999/41YH53SB](#) [D38999/41YH53SC](#) [D38999/41YH53SD](#) [D38999/41YH53SK](#) [D38999/41YH53SN](#)
[D38999/41YH53ZA](#) [D38999/41YH53ZB](#) [D38999/41YH53ZC](#) [D38999/41YH53ZD](#) [D38999/41YH53ZK](#)
[D38999/41YH53ZN](#) [234-100-H5Z111-05PN](#) [234-100-H5ZL11-05PC](#) [234-100-H5ZL11-05PA](#) [234-100-H5ZL11-05PB](#)
[234-100-H8Z117-06PN](#) [234-100-H8Z111-05PN](#) [234-100-H2ZL15-35CD](#) [234-100-H2ZL11-35DN](#) [234-100-H2ZL13-35DN](#) [234-100-H2ZL11-35CA](#) [234-100-H2ZL13-35DA](#) [234-100-H2Z111-35SA](#) [234-100-H2ZL11-35CN](#) [234-100-H2ZL15-35CB](#) [234-100-H2ZL15-35CK](#) [234-100-H2Z111-99PA](#) [230-010P15-35CC](#) [230-010P15-35CN](#) [230-010Z111-35PN](#) [230-010P15-35PN](#) [230-010Z111-99PN](#) [230-010Z115-35PN](#) [230-010P11-05XN](#) [230-010P11-35PN](#) [230-010P11-05PN](#) [230-010Z111-98PN](#) [230-010Z115-35PA](#) [230-010Z111-35PB](#) [230-010Z111-05PN](#) [230-010Z115-18PB](#)
[230-010Z111-35CN](#) [230-010P13-35CN](#) [230-010P15-35CA](#) [230-010Z113-98PN](#) [234-100-H2Z113-35PN](#) [234-100-H2ZL13-35SN](#) [234-100-H2ZL15-35DA](#) [234-100-H2ZL15-35DN](#) [234-100-H2ZL15-35SA](#) [234-100-H2ZL15-35SN](#) [230-010P11-35CA](#) [230-010P11-35CN](#) [230-010P15-35CB](#) [230-010P15-35CD](#) [230-010P15-35CK](#) [230-010Z111-99PA](#)
[230-010Z113-35PN](#)