

Series 803 "Mighty Mouse" 1/4 Turn Bayonet Coupling

Glenair

Series 803

Series 803 ASAP Cordsets For Harsh Environments



**Series 803 Overmolded
ASAP Cordset**

Glenair's ASAP "Mighty Mouse" Overmolded Cordsets offer splashproof protection and excellent cold temperature flexibility. These cables are 100% tested and ready to use. Standard overmolded cables feature polyurethane jackets.

Two Jacket Types – Extruded Estane polyurethane jacket resists abrasion and chemicals. Or choose low smoke/ zero halogen polyurethane jackets for compliance with toxicity regulations.

Shielded – These cables feature 90% coverage tinned copper braid. Cable shields terminate directly to connectors with stainless steel **BAND-IT®** straps.


Simplified Ordering, No Minimums
ASAP cordsets are made-to-order from stocked connectors and cable. Choose #22 or #24 AWG cable with standard Estane jacket for best availability.

HOW TO ORDER


Sample Part Number

803-008	-A	C	4	M	7-10	P	N	-72
Series	End A Connector	End B Connector	Wire Size	Shell Material / Finish	Insert Arr.	Protective Cover	Shell Key Pos.	Length
803-008 Overmolded Cordset, Shielded, with Polyurethane Cable Jacket	-A Plug, with Male Pin Contacts	A Plug, with Male Pin Contacts	2 #22 AWG (Std.)	M Aluminum / Electroless Nickel	5-3 3 #23 6-1 1 #16 6-4 4 #23 6-7 7 #23 7-1 1 #12 7-10 10 #23	P Metal Protective Covers Included	N Normal	Overall Length In Inches
803-009 Overmolded Cordset, Shielded, with Low Smoke/ Zero Halogen Polyurethane Jacket	-B Plug, with Female Socket Contacts	B Plug, with Female Socket Contacts	4 #24 AWG (Std.)	NF Aluminum / Cadmium with Olive Drab Chromate	7-1 1 #12 8-13 13 #23 9-4 4 #16 9-19 19 #23	N No Covers Supplied	X Pos. X	12 Inch Min.
	-C Receptacle, with Male Pin Contacts	C Receptacle, with Male Pin Contacts	6 #26 AWG	ZN Aluminum / Zinc-Nickel with Olive Drab Chromate	10-26 26 #23 12-2 2 #12 12-37 37 #23 14-55 55 #23 15-85 85 #23		Y Pos. Y	
	-D Receptacle, with Female Socket Contacts	D Receptacle, with Female Socket Contacts	8 #28 AWG	ZNU Aluminum / Zinc-Nickel with Black Chromate			Z Pos. Z	
		N No Connector (Single-Ended)		Z1 Stainless Steel / Passivated				

Series 803 "Mighty Mouse" 1/4 Turn Bayonet Coupling



RIGHT ANGLE CORDSETS



How To Order Right Angle Cordsets

Insert the letter "R" after the End A or End B Connector letter designator.

Example

Straight cable 803-008-AC4M6-4PN-72
Right Angle 803-008-**ARC**R4M6-4PN-72

DIMENSIONS

Shell Size	A Max.		B Max.		C Max.		D Max.		E Max.	
	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.
5	2.000	50.80	.490	12.45	1.500	38.10	.490	12.45	1.650	41.91
6	2.500	63.50	.560	14.22	1.500	38.10	.560	14.22	1.650	41.91
7	2.500	63.50	.680	17.27	1.700	43.18	.680	17.27	1.700	43.18
8	2.500	63.50	.740	18.80	1.750	44.45	.740	18.80	1.750	44.45
9	2.500	63.50	.810	20.57	1.750	44.45	.810	20.57	1.750	44.45
10	2.750	69.85	.870	22.10	1.750	44.45	.870	22.10	1.750	44.45
12	3.000	76.20	.930	23.62	1.750	44.45	.930	23.62	1.750	44.45
14	3.500	88.90	1.120	28.45	1.750	44.50	1.120	28.45	1.750	44.45
15	3.750	95.25	1.180	29.97	2.000	50.80	1.180	29.97	2.000	50.80

HARSH ENVIRONMENT CORDSET SPECIFICATIONS

Cable Jacket Material	Thermoplastic Polyurethane, Black, UL 94 V-0 Rated
Cable Shield	Tin-Coated Copper Braid, 90% Minimum Coverage
Conductors	Silver Coated Stranded Wire, TFE Insulated, Per M22759/11
BAND-IT® Shield Termination Band	Stainless Steel
Current Rating	Up to 5 AMP Continuous Duty With #22 AWG Wire
Test Voltage (Dielectric Withstanding Voltage)	500 VAC RMS sea level, 100 VAC RMS 70,000 feet
Insulation Resistance	200 megohms minimum
Operating Temperature	-30° C. to +105° C.
Water Resistance	Splashproof
Solvent Resistance, Polyamide Overmold	Excellent Resistance to Most Solvents, Fuels, and Oils; Poor Resistance to Strong Acids and Bipolar Solvents (Alcohol)
Shielding Effectiveness	40 dB minimum from 100MHz to 1000MHz.
Flammability and Toxicity (LSZH Jacket)	Toxicity Index 3.9 per NES 713 Oxygen Index 28% per ASTM D-2863 Smoke Index 24 per NES 711

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[803-008-AA2NF919PN72](#) [803-008BB2NF1237PN48](#) [803-008-AA2NF919PN48](#)