



MS27469 Wall Mount Hermetic Receptacle MIL-DTL-38999 Series I

How To Order: MS



MS27469 Wall Mount Hermetic Receptacle MIL-DTL-38999 Series I



D38999 QPL
Hermetics

How To Order: Commercial




TABLE I: CONNECTOR DIMENSIONS



SHELL SIZE	A BSC	B SQ ±.016(0.4)	ø C HOLES	D THREADS
9/09	.719(18.3)	.938(23.8)	.133(3.4) .123(3.1)	.6875-24 UNEF-2A
11	.812(20.6)	1.031(26.2)	.133(3.4) .123(3.1)	.8125-20 UNEF-2A
13	.906(23.0)	1.125(28.6)	.133(3.4) .123(3.1)	.9375-20 UNEF-2A
15	.969(24.6)	1.219(31.0)	.133(3.4) .123(3.1)	1.0625-18 UNEF-2A
17	1.062(27.0)	1.312(33.3)	.133(3.4) .123(3.1)	1.1875-18 UNEF-2A
19	1.156(29.4)	1.438(36.5)	.133(3.4) .123(3.1)	1.3125-18 UNEF-2A
21	1.250(31.8)	1.562(39.7)	.133(3.4) .123(3.1)	1.4375-10 UNEF-2A
23	1.375(34.9)	1.688(42.9)	.157(4.0) .142(3.6)	1.5625-18 UNEF-2A
25	1.500(38.1)	1.812(46.0)	.157(4.0) .142(3.6)	1.6875-18 UNEF-2A

TABLE I (CONTINUED):
CONNECTOR DIMENSIONS

SHELL SIZE	ø G HOLES ±.005(0.1)	ø H MIN	ø J MIN	K ±.005(0.1)
9/09	.128(3.3)	.656(16.7)	.516(13.1)	.719(18.3)
11	.128(3.3)	.781(19.8)	.625(15.9)	.812(20.6)
13	.128(3.3)	.921(23.4)	.750(19.1)	.906(23.0)
15	.128(3.3)	1.047(26.6)	.906(23.0)	.968(24.6)
17	.128(3.3)	1.218(30.9)	1.016(25.8)	1.062(27.0)
19	.128(3.3)	1.296(32.9)	1.142(29.0)	1.156(29.4)
21	.128(3.3)	1.421(36.1)	1.266(32.2)	1.250(31.8)
23	.154(3.9)	1.546(39.3)	1.375(34.9)	1.375(34.9)
25	.154(3.9)	1.672(42.5)	1.484(37.7)	1.500(38.1)

TABLE II: CONTACT SIZE

PRINTED CIRCUIT TAIL CONFIGURATIONS
CONTACT STYLE C AND D



Contact Size	ø P
22D	.011 (0.28) .015 (0.38)
20	.024 (0.61) .028 (0.71)
16	.0635 (1.61) .0615 (1.56)
12	.095 (2.41) .093 (2.36)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[MS27469Y13E98P](#) [MS27469Y15D18S](#) [MS27469Y15D35P](#) [MS27469Y19D11P](#) [MS27469Y9E35P](#) [231-100-H0FT09-35PN](#) [231-100-H0FT11-98SN](#) [231-100-H0FT13-35PN](#) [231-100-H0FT15-18SN](#) [231-100-H0FT15-35PN](#) [231-100-H0FT19-11PN](#) [231-100-H0FT25-43PN](#) [231-100-H0Z109-35PN](#) [231-100-H0Z109-35SN](#) [231-100-H0Z109-98PN](#) [231-100-H0Z113-04CN](#) [231-100-H0Z113-35CN](#) [231-100-H0Z113-98PN](#) [231-100-H0Z119-32PN](#) [231-100-H0Z121-11PN](#) [231-100-H0ZL09-98PN](#) [231-100-H0ZL11-35PN](#) [231-100-H0ZL15-97PA](#) [231-100-H0ZL15-97SN](#) [231-100-H0ZL17-26CN](#) [231-100-H0ZL17-26PA](#) [231-100-H0ZL17-26PN](#) [MS27469Y25D43P](#) [MS27469Y15N97S](#) [MS27469Y17N26PA](#) [MS27469Y21E11P](#) [MS27469Y15N35P](#) [MS27469Y23N35P](#) [231-100-H0ZL11-35PA](#) [MS27469Y11N2P](#) [MS27469Y9N35S](#) [MS27469Y15E35S](#) [MS27469Y11E35S](#) [MS27469Y11N2PA](#) [231-100-H0Z113-35SN](#) [231-100-H0Z115-35SN](#) [231-100-H0Z117-35SN](#) [231-100-H0Z115-35PN](#) [231-100-H0ZL23-35PN](#) [231-100-H0Z119-11PN](#) [231-100-H0Z119-11SN](#) [231-100-H0ZL15-35PN](#) [231-100-H0Z111-35SN](#) [231-100-H0Z113-35PN](#) [231-100-H0Z117-35PN](#)