

330-001 and 330-002 Pipe Thread Adapters Rotatable Coupling

CONNECTOR DESIGNATORS **A-F-H-L-S** ROTATABLE COUPLING

Product Series — **330 F S 001 M 16 03-5**

Connector Designator — **F**

Angle and Profile — **S** = Straight

Basic Part No. — **001** = External Thread
002 = Internal Thread

Length Designator (1/2 inch increments: e.g. 5=2.5 inches, Minimum Lengths Table III)

Cable Entry (Table III)

Shell Size (Table I)

Finish (Table II)




TABLE II: STANDARD FINISHES

GLENAIR SYMBOL	FINISH
B	Cadmium Plate, Olive Drab
C	Anodize, Black
G	Hard Coat, Anodic
M	Electroless Nickel
NF	Cadmium Plate, Olive Drab Over Electroless Nickel

See Back Cover for Complete Finish Information and Additional Finish Options

See inside back cover fold-out or pages 13 and 14 for unabridged Tables I and II.

-445 Now Available with the "NESTOR"

Add "-445" to Specify Glenair's Non-Detent, Spring-Loaded, Self-Locking Coupling. See Page 41 for Details.

TABLE III: CABLE ENTRY

Dash No.	Pipe Thread	E	F Dia	G Dia	Length		
					Min	Desig.	
01	1/8	.391 (9.9)	.405 (10.3)	.500 (12.7)	1.5 (38.1)	3	
02	1/4	.593 (15.1)	.540 (13.7)	.625 (15.9)	1.5 (38.1)	3	
03	3/8	.593 (15.1)	.675 (17.1)	.875 (22.2)	1.5 (38.1)	3	
04	1/2	.781 (19.8)	.840 (21.3)	1.000 (25.4)	2.0 (50.8)	4	
05	3/4	.812 (20.6)	1.050 (26.7)	1.250 (31.8)	2.0 (50.8)	4	
06	1	1.000 (25.4)	1.315 (33.4)	1.500 (38.1)	2.0 (50.8)	4	
07	1 1/4	1.031 (26.2)	1.660 (42.2)	1.750 (44.5)	2.5 (63.5)	5	
08	1 1/2	1.031 (26.2)	1.900 (48.3)	2.125 (54.0)	2.5 (63.5)	5	
09	2	1.062 (27.0)	2.375 (60.3)	2.500 (63.5)	2.5 (63.5)	5	
10	2 1/2	1.453 (36.9)	2.875 (73.0)	3.250 (82.6)	2.5 (63.5)	5	

1. Pipe threads per American standard taper pipe thread.
2. Metric dimensions (mm) are indicated in parentheses.
3. O-Ring not supplied with Connector Designator A.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[330FS002N1404-4](#) [330HS002Z11704-6](#) [330AS001M1004-4](#) [330AS001N1004-4](#) [330AS002B1004-5](#)
[330AS002M1406-4](#) [330AS002M6106-4](#) [330AS002N1805-5](#) [330FS001NF2206-4](#) [330HS001M1505-4](#)
[330HS002M2507-6](#) [330HS001N1706-4](#) [330AS002B1604-4](#) [330AS001N2005-4](#) [330FS001B2406-4](#) [330AS001N1605-](#)
[4](#)