



500-047 EMI/RFI Elliptical Banding Backshell



Elliptical Backshells provide extra room for large wire bundles. This one piece version features an oversize shield termination area for both standard and micro BandMaster™ ATS shield termination straps.



Materials

- Shell: Aluminum Alloy 6061 -T6
- Clips: 17-7PH Stainless Steel
- Hardware: 300 Series Stainless Steel


How To Order EMI/RFI Elliptical Backshells

Sample Part Number	500-047	M	25	H	
Series	500-047				
Shell Finish	E – Chem Film (Alodyne) J – Cadmium, Yellow Chromate M – Electroless Nickel NF – Cadmium, Olive Drab Z2 – Gold				
Connector Size	09, 15, 21, 25, 31, 37 51, 51-2, 67, 69, 100 (See Table I)				
Hardware Option	B – Fillister Head Jackscrew H – Hex Head Jackscrew E – Extended Jackscrew F – Jackpost, Female (See Table I)				
EMI Band Strap Option	Omit (Leave Blank) – Band Not Included B – Standard Band .250" Wide M – Micro Band .125" Wide				


Table I: Dimensions




CODE B
FILLISTER HEAD
JACKSCREW



CODE H
HEX HEAD
JACKSCREW



CODE F
FEMALE
JACKPOST



CODE E
EXTENDED
JACKSCREW

Size	A Max.		B Max.		C		D Max.		E		F Max.		G Max.		H Max.	
	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In. ± .015	mm. ± 0.38	In.	mm.	In.	mm.	In.	mm.
09	.850	21.59	.370	9.40	.565	14.35	.312	7.92	.281	7.14	.450	11.43	.481	12.22	.780	19.81
15	1.000	25.40	.370	9.40	.715	18.16	.420	10.67	.281	7.14	.450	11.43	.589	14.96	.910	23.11
21	1.150	29.21	.370	9.40	.865	21.97	.591	15.01	.281	7.14	.450	11.43	.759	19.28	1.030	26.16
25	1.250	31.75	.370	9.40	.965	24.51	.690	17.53	.281	7.14	.450	11.43	.859	21.82	1.090	27.68
31	1.400	35.56	.370	9.40	1.115	28.32	.820	20.83	.281	7.14	.450	11.43	.989	25.12	1.150	29.21
37	1.550	39.37	.370	9.40	1.265	32.13	.970	24.64	.281	7.14	.450	11.43	1.139	28.93	1.180	29.97
51	1.500	38.10	.410	10.41	1.215	30.86	.920	23.37	.312	7.92	.481	12.22	1.089	27.66	1.220	30.99
51-2	1.910	48.51	.370	9.40	1.615	41.02	1.030	26.16	.281	7.14	.450	11.43	1.489	37.82	1.220	30.99
67	2.310	58.67	.370	9.40	2.015	51.18	1.720	43.69	.281	7.14	.450	11.43	1.889	47.98	1.220	30.99
69	1.810	45.97	.410	10.41	1.515	38.48	1.220	30.99	.312	7.92	.481	12.22	1.389	35.28	1.220	30.99
100	2.235	56.77	.460	11.68	1.800	45.72	1.290	32.77	.360	9.14	.529	13.44	1.459	37.06	1.280	32.51

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[500-047M15FB](#) [500-047J100B](#) [500-047J15HB](#) [500-047J31HB](#) [500-047J37B](#) [500-047J51B](#) [500-047J51E](#) [500-047M09BB](#) [500-047M51B](#) [500-047NF100B](#) [500-047NF15H](#) [500-047J25HB](#) [500-047M100B](#) [500-047M37FB](#) [500-047M51BB](#) [500-047J100HB](#) [500-047J37HB](#) [500-047J51HB](#) [500-047M25BB](#) [500-047NF51EB](#) [500-047NF37EB](#) [500-047M37EM](#) [500-047M21E](#) [500-047M15F](#) [500-047M31EB](#) [500-047M69HB](#) [500-047NF09EB](#) [500-047M100BB](#) [500-047M51-2HB](#) [500-047NF15EB](#) [500-047M51EB](#) [500-047M31B](#) [500-047M21B](#) [500-047M15EB](#) [500-047M21EB](#)