




IPT 01 G In-Line Cable Connector with Shrink Boot Backshell



Application Notes

1. In-line cable connector with sealing grommet and backshell for heat shrink boot.
2. Connector/Backshell Class "G" (environmental)—Wire sealing grommet supplied.
3. Standard materials configuration consists of aluminum alloy with stainless steel coupling pins.
4. Standard contact material consists of copper alloy with gold plating over nickel.
5. A broad range of other front and rear connector accessories are available. See our website and/or contact factory for complete information.
6. Standard insert is high insulation synthetic rubber.

IPT 01 G
In-Line Cable Connector
 with Shrink Boot Backshell



IPT Series
 Bayonet Lock
 Connectors

TABLE I: DIMENSIONS

Shell size	A ±0.1	ØB +0.1 -0	ØC +0 -0.1	ØD +0 -0.3	L Max.	ØG ±0.2
8	12.2	8.20	13.0	15.5	43.5	17.3
10	12.2	11.40	15.8	18.3	42.0	21.8
12	12.2	14.55	21.0	23.6	42.0	25.1
14	12.2	17.50	21.8	24.4	42.0	28.6
16	14.5	20.60	25.9	29.7	44.0	30.6
18	14.5	23.15	28.2	31.9	44.5	33.2
20	15.8	26.50	32.2	36.0	48.5	36.5
22	15.8	29.60	34.5	38.4	48.5	39.6
24	14.9	32.80	37.6	41.5	48.5	43.1

TABLE II: MODIFICATION CODES

CONTACT OPTIONS	
Sym	Description
B0	Connector Without Contacts (Only for crimp version)
FINISH OPTIONS	
Sym	Description and RoHS compliant
F6	Black Electrodeposited Paint
F7	Black Zinc Nickel
F11	Electroless Nickel
MB	Marine Bronze
Omit for standard version (Cadmium Olive Drab Finish)	

C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[IPT01G10-6SF7](#)