

SERIES 77 ENVIRONMENTAL SHRINK BOOTS



Glenair Environmental Shrink Boots Now TACOM Approved, In-Stock and Ready for Immediate Shipment

High-performance Series 77 "Full Nelson" environmental shrink boots manufactured by Glenair in Glendale, California are now approved by the US Army Tank-Automotive Command (TACOM). Manufactured from high-temperature crosslinked elastomeric polymer material and/or caustic chemical-resistant Viton polymer, Glenair straight and right angle long-tail shrink boots, Y and T transitions, convoluted strain-relief boots and heat-shrinkable adapter shims have been added to the following source control documentation:

Glenair Series 77 "Full Nelson" TACOM APPROVED Shrink Boots

Description	Military Part Number	Glenair Part Number	Raychem Part Number	Hellermann Part Number	Description	Military Part Number	Glenair Part Number	Raychem Part Number	Hellermann Part Number
Heat Shrinkable Low Profile 3-Entry "Y" Transition	12273148-1**	770-009Y*05	381A301-**	492H412-*	Heat Shrinkable Straight Lipped 2-Entry Long Tail Boot	12273147-1**	770-020S*02	202F211-**	313F322-*
	12273148-2**	770-009Y*06	381A302-**	492H413-*		12273147-2**	770-020S*03	202F221-**	313F332-*
	12273148-3**	770-009Y*07-01	381A303-*01	492H414-*01		12273147-3**	770-020S*04	202F232-**	313F343-*
	12273148-4**	770-009Y*08-01	381A304-*01	492H415-*01		12273147-4**	770-020S*05	202F242-**	313F353-*
	12273148-5**	770-009Y*07	381A303-**	—		12273147-5**	770-020S*06	202F253-**	313F364-*
Heat Shrinkable Low Profile 3-Entry "T" Transition	12273162-1**	770-012T*01	301A511-**	412H622-*	Heat Shrinkable 90° Lipped 2-Entry Long Tail Boot	12273147-6**	770-020S*07	202F263-**	313F374-*
	12273162-2**	770-012T*02	301A512-**	412H623-*		12273147-7**	770-020S*08	202F274-**	313F385-*
	12273162-3**	770-012T*03	301A513-**	412H624-*		12273176-1**	770-021A*02	222F211-**	333F322-*
	12273162-4**	770-012T*04	301A514-**	412H625-*		12273176-2**	770-021A*03	222F221-**	333F332-*
Heat Shrinkable Low Profile 4-Entry 3:1 Transition	12273163-1**	770-014*09	462A421-**	573H532-*	Heat Shrinkable 90° Lipped 2-Entry Long Tail Boot	12273176-3**	770-021A*04	222F232-**	333F343-*
	12273163-2**	770-014*10	462A422-**	573H533-*		12273176-4**	770-021A*05	222F242-**	333F353-*
	12273163-3**	770-014*11	462A423-**	573H534-*		12273176-5**	770-021A*06	222F253-**	333F364-*
	12273163-4**	770-014*12	462A424-**	573H535-*		12273176-6**	770-021A*07	222F263-**	333F374-*
Heat Shrinkable Adapter Shim Boot	12273164-1**	770-019SB*01	202E334-**	313E445-*		12273176-7**	770-021A*08	222F274-**	333F385-*
	12273164-2**	770-019SB*02	202E344-**	313E455-*					
	12273164-3**	770-019SB*03	202E336-**	313E447-*					
	12273164-4**	770-019SB*04	202E346-**	313E457-*					
Heat Shrinkable Convoluted Strain Relief 2-Entry Boot	12273242-1**	770-022C*01	202C611-**	313C722-9					
	12273242-2**	770-022C*02	202C621-**	313C732-9					
	12273242-3**	770-022C*03	202C632-**	313C743-9					
	12273242-4**	770-022C*04	202C642-**	313C753-9					
	12273242-5**	770-022C*05	202C653-**	313C764-9					
	12273242-6**	—	202G621-**	—					
	12273242-7**	—	202G632-**	—					
	12273242-8**	—	202C642-**	—					
	12273242-9**	—	202C653-**	—					



For more information
contact Glenair at
818-247-6000 or
visit our website at
www.glenair.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[770-022C603W1](#) [770-022C704](#) [770-021A503](#) [770-012T502](#) [770-012T603](#) [770-020S604](#) [770-009Y605W1](#) [770-022C103](#) [770-022C501R](#) [770-022C702W2](#) [770-012T601](#) [770-009Y507W1](#) [770-022C106](#) [770-021A606W1](#) [770-022C602W3](#) [770-022C601](#) [770-021A602](#) [770-022C601W1](#) [770-022C701W2](#) [770-020S606](#) [770-020S602W1](#) [770-020S503](#) [770-020S605](#) [770-021A602W1](#) [770-022C502W1](#) [770-022C505](#) [770-019SB601](#) [770-022C703W1](#) [770-014609](#) [770-022C501](#) [770-020S602](#) [770-019SB602](#) [770-022C702](#) [770-022C602W1](#) [770-012T501](#) [770-019SB602W3](#) [770-022C703W2](#) [770-021A702](#) [770-012T604](#) [770-014509](#) [770-014510](#) [770-022C504](#) [770-021A504](#) [770-009Y605](#) [770-022C701](#) [770-021A703](#) [770-019SB603](#) [770-020S607W1](#) [770-022C604W1](#) [770-022C703](#) [770-012T602](#) [770-019SB601W3](#) [770-022C702W1](#) [770-022C705](#) [770-021A502](#) [770-014609W3](#) [770-022C603W3](#) [770-021A606](#) [770-009Y505](#) [770-020S504](#) [770-022C605](#) [770-021A608](#) [770-014611](#) [770-009Y607](#) [770-009Y606](#) [770-020S603W1](#) [770-020S607](#) [770-020S608](#) [770-009Y607-01](#) [770-021A602W3](#) [770-021A606W3](#) [770-020S602W3](#) [770-022C704W1](#) [770-022C506](#) [770-020S505](#) [770-020S606W3](#) [770-020S506](#) [770-020S507](#) [770-019SB603W3](#) [770-019SB604](#) [770-020S603W3](#) [770-022C503](#) [770-012T503](#) [770-009Y506](#) [770-022C701W1](#) [770-009Y507](#) [770-022C502](#) [770-022C605W1](#)