



Quality Products. Service Excellence.

Type 4 Mild Steel Two Door Floormount Enclosure 1422 N4 FM Series

Continuous Hinge Door with Clamps



Application

- Designed to house electrical, electronic, hydraulic or pneumatic controls and instruments
- Provides protection where equipment may be hosed down or otherwise be very wet, or in outdoor applications for full weather protection.

Standards

- UL 508A Type 3R, 4 and 12
- CSA Type 3R, 4 and 12
- Complies with
 - NEMA Type 3R, 4 12 and 13
 - IEC 60529, IP66

Construction

- Enclosures are formed steel - 12 gauge (60" high) or combination 10/12 gauge (72" high)
- Smooth, continuously welded seams without knockouts, cutouts or holes.
- Body stiffeners are provided in the larger enclosures for extra rigidity.
- Heavy duty lifting eyebolts are provided with reinforcing support angles.
- Center post is removable for easy installation of the inner panel.
- Formed lip on door and top of enclosure opening exclude flowing liquids and contaminants.
- Continuously hinged doors may be removed by pulling the stainless steel hinge pin.
- Doors are secured with heavy duty stainless steel clamps.
- Provision for padlocking.
- 12" floor stands are welded to the enclosure.
- Seamless poured-in place gasket.
- Provision for light kit mounting.
- A removable 10 gauge inner panel is included.
- Panel supports are provided for easy panel installation.
- Collar studs are provided for mounting inner panels.
- A bonding stud is provided on the door and a grounding stud is provided in the enclosure for each door.
- A literature pocket is provided for the inside of the door.

Finish

- Cover and enclosure are finished in recoatable smooth ANSI 61 gray powder coating.
- Removable white inner panel is finished in white powder coating.

Accessories

- Additional Inner Panels
- Barrier Kits for Type 4 Floormount
- Enclosure Stabilizers
- Window Kits
- General Accessories
- Door Stop Kit
- Drip Shield Kit
- Climate Control
- Lighting

**New and improved PDF part
drawing files with more detail
now available.**

Click part number in table below
to access PDF, DXF, and STEP files.

| w/ Feet | Enclosure | | | Panel | |
|------------|-----------|-------|-------|-------|-------|
| Part No. | H | W | D | H | W |
| 1422N4B10F | 60.13 | 48.06 | 10.69 | 56.00 | 44.00 |
| 1422N4D12F | 60.13 | 60.06 | 12.69 | 56.00 | 56.00 |
| 1422N4E12F | 72.13 | 60.06 | 12.69 | 68.00 | 56.00 |
| 1422N4F12F | 72.13 | 72.06 | 12.69 | 68.00 | 68.00 |
| 1422N4F24F | 72.13 | 72.06 | 24.69 | 68.00 | 68.00 |

Tags: 1422, floormount, two door, steel, Type 4, NEMA 4, pneumatic, hydraulic, instrument, inner panel, continuous hinge, clamps

Data subject to change without notice

© 2025. Hammond Manufacturing Ltd. All rights reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[1422N4D12F](#) [1422N4E12F](#) [1422N4B10F](#) [1422N4F24F](#) [1422N4F12F](#)