



Quality Products. Service Excellence.

Type 4/12 Wiring Trough 1486 Series

NEW SIZES



Application

- Designed to enclose and protect multiple wiring junctions from dirt, dust, oil and water.

Standards

- UL 870 Type 1, 12, 4
- CSA Type 1, 12, 4
- Complies with
 - NEMA Type 12, 4
 - IEC 60529, IP66

Construction

- Formed 14 gauge steel.
- Smooth continuously welded seams.
- Butt hinged cover is secured with easily operated stainless steel screw clamps.
- Oil resistant gaskets are permanently secured.
- 12 gauge external mounting feet are welded to the back.

Finish

- Troughs and covers are finished in ANSI 61 gray powder coating.



Part No.	Enclosure		
	H	D	L
1486B12	2.50	2.50	12.00
1486B18	2.50	2.50	18.00
1486B24	2.50	2.50	24.00
1486B30	2.50	2.50	30.00
1486B36	2.50	2.50	36.00
1486B48	2.50	2.50	48.00
1486B60	2.50	2.50	60.00
1486B72	2.50	2.50	72.00
1486C12	4.00	4.00	12.00
1486C18	4.00	4.00	18.00
1486C24	4.00	4.00	24.00
1486C30	4.00	4.00	30.00
1486C36	4.00	4.00	36.00
1486C48	4.00	4.00	48.00
1486C60	4.00	4.00	60.00
1486C72	4.00	4.00	72.00
1486D12	6.00	6.00	12.00
1486D18	6.00	6.00	18.00
1486D24	6.00	6.00	24.00
1486D30	6.00	6.00	30.00
1486D36	6.00	6.00	36.00
1486D48	6.00	6.00	48.00
1486D60	6.00	6.00	60.00
1486D72	6.00	6.00	72.00

Part No.	Enclosure		
	H	D	L
1486E12	8.00	8.00	12.00
1486E24	8.00	8.00	24.00
1486E36	8.00	8.00	36.00
1486E48	8.00	8.00	48.00
1486E60	8.00	8.00	60.00
1486G24	12.00	12.00	24.00
1486G36	12.00	12.00	36.00
1486G48	12.00	12.00	48.00
1486G60	12.00	12.00	60.00

Tags: 1486, wiring, trough, Type 4, Type 12, hinged cover

Data subject to change without notice

© 2025. Hammond Manufacturing Ltd. All rights reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[1486D24](#) [1486C36](#) [1486D60](#) [1486D18](#) [1486D48](#) [1486D12](#) [1486D36](#) [1486D30](#) [1486D72](#) [1486C30](#) [1486C18](#)
[1486C72](#) [1486C60](#) [1486C12](#) [1486B60](#) [1486B18](#) [1486B30](#) [1486B12](#) [1486B36](#) [1486B24](#) [1486B48](#) [1486B72](#)
[1486C48](#) [1486C24](#) [1486E12](#) [1486E24](#) [1486E36](#) [1486E48](#) [1486E60](#) [1486G24](#) [1486G36](#) [1486G48](#) [1486G60](#)