



Quality Products. Service Excellence.

Rack Mount Basic PDU with Shielded Cord 1583-V Series

15A or 20A | Single-Phase 125V | Rear Facing 5-15R or 5-20R Outlets

Features



- Designed for power distribution from the rear of the unit, and where electromagnetic or radio frequency interference is a concern.
- 1U horizontal 19" rackmount installation.
- Shielded cord reduces EMI/ RFI and "dirty" power from utilities.
- Shielding is by way of 100% coverage in aluminum mylar foil with a 20 gauge drain wire.
- Includes on/off switch and circuit breaker
- Includes (8) rear-facing outlets

Specifications

- Heavy-duty cord, either 12 gauge (12/3 SJT) or 14 gauge (14/3 SJT) wire for extreme temperature ranges and integral moulded plug.
- Plug types for 15 Amp models are NEMA 5-15P straight blade or NEMA L5-15P locking type.
- Plug types for 20 Amp models are NEMA 5-20P straight blade or NEMA L5-20P locking type.
- Includes 15 Amp or 20 Amp 125 VAC circuit breaker to prevent accidental overload.
- UL/cUL recognized Standard UL1363 file No. E166039 & CSA C22.2 No. 308-14 & CSA C22.2 No. 0.4-04
- Finished in textured RAL9005 black powder paint finish.
- TAA-compliant for GSA Schedule purchases.
- RoHS and REACH compliant.
- Manufactured in North America.



Plug Types



5-15P Straight Blade

L5-15P Locking Type

5-20P Straight Blade

L5-20P Locking Type

Gallery



Accessories

- Mounting Hardware
- Rail Depth Adapter Kit

| Part Number | Height | Width | Depth | Rack Units | Number of Outlets | Current Rating | NEMA Outlet Type | Cord Length | Plug Blade Type | NEMA Plug Type |
|---------------|--------|-------|-------|------------|-------------------|----------------|------------------|-------------|-----------------|----------------|
| 1583H8B1BKV | 1.72 | 19.00 | 2.66 | 1U | 8 | 15A | 5-15R | 15 ft | Straight | 5-15P |
| 1583H8D1BKV | 1.72 | 19.00 | 2.66 | 1U | 8 | 15A | 5-15R | 15 ft | Locking | L5-15P |
| 1589H8G1BKRRV | 1.72 | 19.00 | 2.66 | 1U | 8 | 20A | 5-20R | 15 ft | Straight | 5-20P |
| 1589H8D1BKRRV | 1.72 | 19.00 | 2.66 | 1U | 8 | 20A | 5-20R | 15 ft | Locking | L5-20P |

Data subject to change without notice

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Hammond:

[1589H8G1BKRRV](#) [1583H8B1BKV](#) [1583H8D1BKV](#) [1589H8D1BKRRV](#)