



Quality Products. Service Excellence.

## Heavy Duty Outlet Strip 1589 Series

20A | 125V | 5-15/5-20R Outlets

### Features



- Built to meet the rugged requirements of industrial and commercial use.
- All metal housing – tough extruded aluminum case with black powder-coated steel cover.
- Available with on/off switch or red pilot light to indicate power on.
- Mounting feet (with keyhole slots) allow temporary work station mounting if desired.

### Specifications

- Heavy-duty black receptacles rated for 20A, 125VAC service (NEMA 5-20R, Single T-Slot).
- Heavy-duty power cord – 12/3 SJT for extreme temperature ranges.
- Integral molded plug with straight blade (NEMA 5-20P) or locking (NEMA L5-20P) configuration.
- Includes 20A, 125VAC circuit breaker to prevent accidental line overload.
- CSA certified, Standards C22.2 (No. 21-95 and No. 42-99).
- UL/cUL Listed Standard UL1363 file No. E166039 & CSA C22.2 No. 308-14



### Accessories

- Rack Cabinet Vertical Mount Adaptor



| On/Off Switch<br>Part No. | Illuminated<br>Light Only<br>Part No. | Overall Dimensions |       |        | Outlet<br>Qty | Outlet<br>NEMA Type | Cord<br>Length (ft) | Plug<br>Type | Plug<br>NEMA Type |
|---------------------------|---------------------------------------|--------------------|-------|--------|---------------|---------------------|---------------------|--------------|-------------------|
|                           |                                       | Height             | Width | Length |               |                     |                     |              |                   |
| 1589H4C1                  | 1589T4C1                              | 2.33               | 2.13  | 10.18  | 4             | 5-20R               | 6                   | Locking      | L5-20P            |
| 1589H4D1                  | 1589T4D1                              | 2.33               | 2.13  | 10.18  | 4             | 5-20R               | 15                  | Locking      | L5-20P            |
| 1589H4F1                  | 1589T4F1                              | 2.33               | 2.13  | 10.18  | 4             | 5-20R               | 6                   | Straight     | 5-20P             |
| 1589H4G1                  | 1589T4G1                              | 2.33               | 2.13  | 10.18  | 4             | 5-20R               | 15                  | Straight     | 5-20P             |
| 1589H6C1                  | 1589T6C1                              | 2.33               | 2.13  | 13.36  | 6             | 5-20R               | 6                   | Locking      | L5-20P            |
| 1589H6D1                  | 1589T6D1                              | 2.33               | 2.13  | 13.36  | 6             | 5-20R               | 15                  | Locking      | L5-20P            |
| 1589H6F1                  | 1589T6F1                              | 2.33               | 2.13  | 13.36  | 6             | 5-20R               | 6                   | Straight     | 5-20P             |
| 1589H6G1                  | 1589T6G1                              | 2.33               | 2.13  | 13.36  | 6             | 5-20R               | 15                  | Straight     | 5-20P             |
| 1589H8C1                  | 1589T8C1                              | 2.33               | 2.13  | 16.51  | 8             | 5-20R               | 6                   | Locking      | L5-20P            |
| 1589H8D1                  | 1589T8D1                              | 2.33               | 2.13  | 16.51  | 8             | 5-20R               | 15                  | Locking      | L5-20P            |

| On/Off Switch<br>Part No. | Illuminated<br>Light Only<br>Part No. | Overall Dimensions |       |        | Outlet<br>Qty | Outlet<br>NEMA Type | Cord<br>Length (ft) | Plug<br>Type | Plug<br>NEMA Type |
|---------------------------|---------------------------------------|--------------------|-------|--------|---------------|---------------------|---------------------|--------------|-------------------|
|                           |                                       | Height             | Width | Length |               |                     |                     |              |                   |
| 1589H8F1                  | 1589T8F1                              | 2.33               | 2.13  | 16.51  | 8             | 5-20R               | 6                   | Straight     | 5-20P             |
| 1589H8G1                  | 1589T8G1                              | 2.33               | 2.13  | 16.51  | 8             | 5-20R               | 15                  | Straight     | 5-20P             |

### Replacement Mounting Foot (One Foot)

| Part No. |
|----------|
| 1584MF   |

*Data subject to change without notice*

© 2021. Hammond Manufacturing Ltd. All rights reserved.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Hammond:

[1589T4C1](#) [1589H6F1](#) [1589H6C1](#) [1589H6D1](#) [1589H6G1](#) [1589H4F1](#) [1589T6F1](#) [1589T6C1](#) [1589T4F1](#) [1589H8F1](#)  
[1589H8C1](#) [1589H8G1](#) [1589H4C1](#) [1589H4G1](#) [1589T8F1](#) [1589T8C1](#) [1589T4G1](#) [1589H4D1](#) [1589T8G1](#)  
[1589T8D1](#) [1589H8D1](#) [1589T4D1](#)