



Quality Products. Service Excellence.

Painted Die-Cast "Stomp Box" Enclosures 1590-STOMP Series

A Selection of Popular Colors & Sizes



WARNING: Many websites sell knockoffs and copies using Hammond part numbers, or "similar to Hammond." Make sure it says Hammond!

Key Features

- Rugged diecast aluminum alloy electronic instrument enclosure.
- Diecast material is tough yet easy to machine.
- Factory powder coated to save stomp box manufacturers and experimenters time and money.
- Coated with a smooth glossy polyester powder coat for a lasting finish, even after machining.
- Smooth finish allows for easy adhesion of labels or silk screens.
- Colors are matched to standard RAL colors.
- Lap joint construction provides protection against access of dust and splashing water. Also provides for improved EMI/RFI shielding.
- Designed to meet IP54. See gasket kit accessory below to meet IP65. IP65 rating also requires water-tight screws.
- Low side wall draft angle (2° or less) for easy PC board mounting.
- Unfinished and textured black versions are also available and in additional sizes and styles - See "Diecast Aluminum" and "Trapezoid and Octagon Diecast".

Replacement Hardware

- Replacement screws - nickel plated, #6-32 x 1/2" - **1590MS100** - Package of 100.
- For an even funkier look - order our black replacement screws, #6-32 x 1/2" - **1590MS50BK** - Package of 50.

Tamper-Resistant Hardware (Upgrade!)

- Tamper-resistant screws - nickel plated, #6-32 x 1/2" - **1590MS50T** - Package of 50.
- Tamper-resistant screws - black, #6-32 x 1/2" - **1590MS50TBK** - Package of 50.

Photo Features:



Hammond stomp box enclosures come in traditional sizes and shapes and well as unique trapezoid and octagon models.

Rectangular Enclosures

Part Number	Color	RAL Number	Length (mm)	Width (mm)	Height (mm)	Optional Gasket
1590ACB	Cobalt Blue	RAL 5013	93	38.5	31	1590AGASKET
1590AGR	Green	RAL 6024	93	38.5	31	1590AGASKET
1590ALG	Light Gray	RAL 7035	93	38.5	31	1590AGASKET
1590AOR	Orange	RAL 2009	93	38.5	31	1590AGASKET
1590APR	Purple	RAL 4008	93	38.5	31	1590AGASKET
1590ARD	Red	RAL 3011	93	38.5	31	1590AGASKET
1590AYL	Yellow	RAL 1021	93	38.5	31	1590AGASKET
1590G2CB	Cobalt Blue	RAL 5013	100	50	31	1590GGASKET
1590G2GR	Green	RAL 6024	100	50	31	1590GGASKET
1590G2LG	Light Gray	RAL 7035	100	50	31	1590GGASKET
1590G2OR	Orange	RAL 2009	100	50	31	1590GGASKET
1590G2PR	Purple	RAL 4008	100	50	31	1590GGASKET
1590G2RD	Red	RAL 3011	100	50	31	1590GGASKET
1590G2YL	Yellow	RAL 1021	100	50	31	1590GGASKET
1590BCB	Cobalt Blue	RAL 5013	112	60.5	31	1590BGASKET
1590BGR	Green	RAL 6024	112	60.5	31	1590BGASKET
1590BLG	Light Gray	RAL 7035	112	60.5	31	1590BGASKET
1590BOR	Orange	RAL 2009	112	60.5	31	1590BGASKET
1590BPR	Purple	RAL 4008	112	60.5	31	1590BGASKET
1590BRD	Red	RAL 3011	112	60.5	31	1590BGASKET
1590BYL	Yellow	RAL 1021	112	60.5	31	1590BGASKET
1590B2CB	Cobalt Blue	RAL 5013	112	60.5	37.5	1590BGASKET
1590B2GR	Green	RAL 6024	112	60.5	37.5	1590BGASKET
1590B2LG	Light Gray	RAL 7035	112	60.5	37.5	1590BGASKET
1590B2OR	Orange	RAL 2009	112	60.5	37.5	1590BGASKET
1590B2PR	Purple	RAL 4008	112	60.5	37.5	1590BGASKET

Part Number	Color	RAL Number	Length (mm)	Width (mm)	Height (mm)	Optional Gasket
1590B2RD	Red	RAL 3011	112	60.5	37.5	1590BGASKET
1590B2YL	Yellow	RAL 1021	112	60.5	37.5	1590BGASKET
1590BSCB	Cobalt Blue	RAL 5013	112	60.5	37.5	1590BGASKET
1590BSGR	Green	RAL 6024	112	60.5	37.5	1590BGASKET
1590BSLG	Light Gray	RAL 7035	112	60.5	37.5	1590BGASKET
1590BSOR	Orange	RAL 2009	112	60.5	37.5	1590BGASKET
1590BSPR	Purple	RAL 4008	112	60.5	37.5	1590BGASKET
1590BSRD	Red	RAL 3011	112	60.5	37.5	1590BGASKET
1590BSYL	Yellow	RAL 1021	112	60.5	37.5	1590BGASKET
1590B3CB	Cobalt Blue	RAL 5013	112	60.5	37.5	1590B3GASKET
1590B3GR	Green	RAL 6024	112	60.5	37.5	1590B3GASKET
1590B3LG	Light Gray	RAL 7035	112	60.5	37.5	1590B3GASKET
1590B3OR	Orange	RAL 2009	112	60.5	37.5	1590B3GASKET
1590B3PR	Purple	RAL 4008	112	60.5	37.5	1590B3GASKET
1590B3RD	Red	RAL 3011	112	60.5	37.5	1590B3GASKET
1590B3YL	Yellow	RAL 1021	112	60.5	37.5	1590B3GASKET
1590BBCB	Cobalt Blue	RAL 5013	119.5	94	34	1590BBGASKET
1590BBGR	Green	RAL 6024	119.5	94	34	1590BBGASKET
1590BBLG	Light Gray	RAL 7035	119.5	94	34	1590BBGASKET
1590BBOR	Orange	RAL 2009	119.5	94	34	1590BBGASKET
1590BBPR	Purple	RAL 4008	119.5	94	34	1590BBGASKET
1590BBRD	Red	RAL 3011	119.5	94	34	1590BBGASKET
1590BBYL	Yellow	RAL 1021	119.5	94	34	1590BBGASKET
1590BB2CB	Cobalt Blue	RAL 5013	119.5	94	34	1590BBGASKET
1590BB2GR	Green	RAL 6024	119.5	94	34	1590BBGASKET
1590BB2LG	Light Gray	RAL 7035	119.5	94	34	1590BBGASKET
1590BB2OR	Orange	RAL 2009	119.5	94	34	1590BBGASKET
1590BB2PR	Purple	RAL 4008	119.5	94	34	1590BBGASKET
1590BB2RD	Red	RAL 3011	119.5	94	34	1590BBGASKET
1590BB2YL	Yellow	RAL 1021	119.5	94	34	1590BBGASKET
1590BBSCB	Cobalt Blue	RAL 5013	119.5	94	42	1590BBGASKET
1590BBSGR	Green	RAL 6024	119.5	94	42	1590BBGASKET
1590BBSLG	Light Gray	RAL 7035	119.5	94	42	1590BBGASKET
1590BBSOR	Orange	RAL 2009	119.5	94	42	1590BBGASKET
1590BBSPR	Purple	RAL 4008	119.5	94	42	1590BBGASKET
1590BBSRD	Red	RAL 3011	119.5	94	42	1590BBGASKET
1590BBSYL	Yellow	RAL 1021	119.5	94	42	1590BBGASKET
1590XXCB	Cobalt Blue	RAL 5013	145	121	40	1590XGASKET
1590XXGR	Green	RAL 6024	145	121	40	1590XGASKET
1590XXLG	Light Gray	RAL 7035	145	121	40	1590XGASKET
1590XXOR	Orange	RAL 2009	145	121	40	1590XGASKET
1590XXPR	Purple	RAL 4008	145	121	40	1590XGASKET
1590XXRD	Red	RAL 3011	145	121	40	1590XGASKET
1590XXYL	Yellow	RAL 1021	145	121	40	1590XGASKET

Trapezoidal and Octagonal Enclosures

Part Number	Color	RAL Number	Shape	Length (mm)	Width at Small End (mm)	Width at Large End (mm)	Depth (mm)
1590TRPBCB	Cobalt Blue	RAL 5013	Narrow Trapezoid	112	61.5	79	39
1590TRPBGR	Green	RAL 6024	Narrow Trapezoid	112	61.5	79	39
1590TRPBLG	Light Gray	RAL 7035	Narrow Trapezoid	112	61.5	79	39
1590TRPBOR	Orange	RAL 2009	Narrow Trapezoid	112	61.5	79	39
1590TRPBPR	Purple	RAL 4008	Narrow Trapezoid	112	61.5	79	39
1590TRPBRD	Red	RAL 3011	Narrow Trapezoid	112	61.5	79	39
1590TRPBYL	Yellow	RAL 1021	Narrow Trapezoid	112	61.5	79	39
1590TRPCCB	Cobalt Blue	RAL 5013	Wide Trapezoid	95	122	151	39

Part Number	Color	RAL Number	Shape	Length (mm)	Width at	Width at	Depth (mm)
					Small End (mm)	Large End (mm)	
1590TRPCGR	Green	RAL 6024	Wide Trapezoid	95	122	151	39
1590TRPCLG	Light Gray	RAL 7035	Wide Trapezoid	95	122	151	39
1590TRPCOR	Orange	RAL 2009	Wide Trapezoid	95	122	151	39
1590TRPCPR	Purple	RAL 4008	Wide Trapezoid	95	122	151	39
1590TRPCRD	Red	RAL 3011	Wide Trapezoid	95	122	151	39
1590TRPCYL	Yellow	RAL 1021	Wide Trapezoid	95	122	151	39
1590STPCCB	Cobalt Blue	RAL 5013	Octagon	133	57	133	39
1590STPCGR	Green	RAL 6024	Octagon	133	57	133	39
1590STPCLG	Light Gray	RAL 7035	Octagon	133	57	133	39
1590STPCOR	Orange	RAL 2009	Octagon	133	57	133	39
1590STPCPR	Purple	RAL 4008	Octagon	133	57	133	39
1590STPCRD	Red	RAL 3011	Octagon	133	57	133	39
1590STPCYL	Yellow	RAL 1021	Octagon	133	57	133	39

Tags: diecast, aluminum, stomp box, screw down lid, pedal box, painted, trapezoid, octagon, colorful Data subject to change without notice

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[1590XXCB](#) [1590XXGR](#)