



Quality Products. Service Excellence.

ABS Plastic Multipurpose Enclosures w/ Card Guides 1591 Series

Flame Retardant, General Purpose, Flanged Lid or Bottom

Key Features



- Ideally suited for vertical mounting of printed circuit boards.
- Card guides are molded into all side walls and accept 1.5 mm (0.062") thick boards.
- Lap joint construction provides protection against access of dust and splashing water.
- Designed to meet IP54.
- Standard versions are molded from easy-to-machine flame retardant ABS plastic which carries a UL flammability rating of UL94 V-0.
- Economy versions are molded from general purpose plastic and are not flame retardant.
- On standard versions the lid is secured with M3 x 10 mm Phillips machine screws, threaded into integral brass bushings. Perfect for applications when repetitive assembly and disassembly are required.
- Economy versions are assembled with self-tapping screws into fully plastic posts.
- Black enclosures include black screws, while light gray enclosures include standard nickel finish screws.

Alternatives

- If EMI/ RFI Shielding is required, try series **1591R**.
- If card guides are not required or horizontal mounting of printed circuit boards is preferred, try series **1591XX**.
- For transparent polycarbonate versions, try series **1591T**.



Photo Features

1591 Series enclosures are available in two colors.

- Light Gray ("GY")
- Black ("BK")



Integral card guides accept

Available with wall mounting

Also available with an

1.5 mm (0.062") PC boards. flanges molded into the lid. accessory flange attached to the bottom.

Machine screws thread into brass bushing to attach the lid.


PC Board Card Adaptors:

- Allows mounting of PC boards horizontally within the enclosure.
- Molded from Flame retardant ABS plastic

Part Number **1591Z6** - Package of 6

Part Number **1591Z50** - Package of 50

Part Number **1591Z100** - Package of 100



Hardware:

- Replacement machine lid screws for standard flame-retardant versions are available in packs of 100: **1591MS100** (nickel plated) or **1591MS100BK** (black).
- Replacement self-tapping lid screws for economy versions are available in packs of 100: **1591TS100** (nickel plated) or **1591TS100BK** (black).

Enclosures Without Mounting Flanges

Flame Retardant ABS Enclosures		General Purpose ABS Enclosures		Length (mm)	Width (mm)	Depth (mm)	Clear Lid Accessory
Black	Gray	Black	Gray				
1591MBK	1591MGY	1591MSBK	1591MSGY	85	56	26	1591LC
1591LBK	1591LGY	1591LSBK	1591LSGY	85	56	39	1591LC
1591ABK	1591AGY	1591ASBK	1591ASGY	100	50	25	1591AC
1591SBK	1591SGY	1591SSBK	1591SSGY	110	82	44	1591SC
1591BBK	1591BGY	1591BSBK	1591BSGY	112	62	31	1591BC
1591CBK	1591CGY	1591CSBK	1591CSGY	120	65	40	1591CC
1591TBK	1591TGY	1591TSBK	1591TSGY	120	80	59	1591TC
1591UBK	1591UGY	1591USBK	1591USGY	120	120	59	1591UC
1591VBK	1591VGY	1591VSBK	1591VSGY	120	120	94	1591VC
1591GBK	1591GGY	1591GSBK	1591GSGY	120.5	94	34	1591GC
1591DBK	1591DGY	1591DSBK	1591DSGY	150	80	50	1591DC
1591HBK	1591HGY	1591HSBK	1591HSGY	166	71	29	1591HC
1591EBK	1591EGY	1591ESBK	1591ESGY	190	111	61	1591EC

Enclosures With Mounting Flanges

Flame Retardant ABS, Flanged Lid		General Purpose ABS, Flanged Lid	Flame Retardant, Bottom Flange		General Purpose ABS, Bottom Flange		Length (mm)	Width (mm)	Depth (mm)	Clear Lid Accessory
Black	Gray	Black	Black	Gray	Black	Gray				
1591MFLBK	1591MFLGY	1591MSFLBK	1591MF2BK	1591MF2GY	1591MF2SBK	1591MF2SGY	85	56	26	1591LC
1591LFLBK	1591LFLGY	1591LSFLBK	1591LF2BK	1591LF2GY	1591LF2SBK	1591LF2SGY	85	56	39	1591LC

Flame Retardant ABS, Flanged Lid		General Purpose ABS, Flanged Lid	Flame Retardant, Bottom Flange		General Purpose ABS, Bottom Flange		Length (mm)	Width (mm)	Depth (mm)	Clear Lid Accessory
Black	Gray	Black	Black	Gray	Black	Gray				
1591AFLBK	1591AFLGY	1591ASFLBK	1591AF2BK	1591AF2GY	1591AF2SBK	1591AF2SGY	100	50	25	1591AC
1591SFLBK	1591SFLGY	1591SSFLBK	1591SF2BK	1591SF2GY	1591SF2SBK	1591SF2SGY	110	82	44	1591SC
1591BFLBK	1591BFLGY	1591BSFLBK	1591BF2BK	1591BF2GY	1591BF2SBK	1591BF2SGY	112	62	31	1591BC
1591CFLBK	1591CFLGY	1591CSFLBK	1591CF2BK	1591CF2GY	1591CF2SBK	1591CF2SGY	120	65	40	1591CC
1591TFLBK	1591TFLGY	1591TSFLBK	1591TF2BK	1591TF2GY	1591TF2SBK	1591TF2SGY	120	80	59	1591TC
1591UFLBK	1591UFLGY	1591USFLBK	1591UF2BK	1591UF2GY	1591UF2SBK	1591UF2SGY	120	120	59	1591UC
1591VFLBK	1591VFLGY	1591VSFLBK	1591VF2BK	1591VF2GY	1591VF2SBK	1591VF2SGY	120	120	94	1591VC
1591GFLBK	1591GFLGY	1591GSFLBK	1591GF2BK	1591GF2GY	1591GF2SBK	1591GF2SGY	120.5	94	34	1591GC
1591DFLBK	1591DFLGY	1591DSFLBK	1591DF2BK	1591DF2GY	1591DF2SBK	1591DF2SGY	150	80	50	1591DC
1591HFLBK	1591HFLGY	1591HSFLBK	1591HF2BK	1591HF2GY	1591HF2SBK	1591HF2SGY	166	71	29	1591HC
1591EFLBK	1591EFLGY	1591ESFLBK	1591EF2BK	1591EF2GY	1591EF2SBK	1591EF2SGY	190	111	61	1591EC

Tags: plastic, card guide, project box, ABS, PCB, flanged, bottom flange, flanged lid, multipurpose

Data subject to change without notice

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[1591SSFLBK](#) [1591MFLBK](#) [1591CSBK](#) [1591HFLBK](#) [1591HFLGY](#) [1591VBK](#) [1591MFLGY](#) [1591BFLGY](#) [1591DSBK](#)
[1591EBK](#) [1591EBG](#) [1591EBU](#) [1591LSBK](#) [1591BSBK](#) [1591GGY](#) [1591GBU](#) [1591GBG](#) [1591LBG](#) [1591SSBK](#)
[1591LBK](#) [1591ABG](#) [1591ABK](#) [1591CBU](#) [1591TSFLBK](#) [1591CBG](#) [1591CBK](#) [1591CFLBK](#) [1591MGY](#) [1591MBG](#)
[1591MBU](#) [1591DC](#) [1591USBK](#) [1591CFLGY](#) [1591Z6](#) [1591TBK](#) [1591LGY](#) [1591LBU](#) [1591SFLGY](#) [1591SFLBK](#)
[1591LFLGY](#) [1591LFLBK](#) [1591UFLBK](#) [1591AGY](#) [1591ABU](#) [1591DBG](#) [1591UBG](#) [1591DBU](#) [1591DGY](#) [1591UBK](#)
[1591UFLGY](#) [1591VSFLBK](#) [1591GFLGY](#) [1591GFLBK](#) [1591GSBK](#) [1591ASFLBK](#) [1591AFLGY](#) [1591VGY](#) [1591HBU](#)
[1591HGY](#) [1591MBK](#) [1591BSFLBK](#) [1591SBU](#) [1591SBG](#) [1591CGY](#) [1591SGY](#) [1591HBK](#) [1591HBG](#) [1591EFLGY](#)
[1591HSFLBK](#) [1591BC](#) [1591UGY](#) [1591UBU](#) [1591CSFLBK](#) [1591EGY](#) [1591DSFLBK](#) [1591GBK](#) [1591DBK](#) [1591EC](#)
[1591LC](#) [1591VC](#) [1591UC](#) [1591CC](#) [1591TC](#) [1591AC](#) [1591HC](#) [1591BFLBK](#) [1591ASBK](#) [1591BBK](#) [1591SC](#)
[1591GC](#) [1591DFLBK](#) [1591TGY](#) [1591TBG](#) [1591DFLGY](#) [1591TBU](#) [1591VFLGY](#) [1591VBG](#) [1591VBU](#) [1591AFLBK](#)
[1591BBG](#)