



"T" Display Enclosures



Key Features:

- Perfect for instrument or mobile data enclosures requiring a keypad and display.
- Available with either a solid display area (1592ETSD) or a versatile opening with a clear lens (1592ETCD).
- Molded from flame retardant ABS plastic, choice of black or grey (material carries a UL flammability rating of 94V-0).
- 1592ETSD offers a solid display area 122 mm x 85 mm (4.8" x 3.4") that will accommodate display boards up to 118 mm x 60 mm (4.6" x 2.37").
- 1592ETCD offers a clear polycarbonate lens 102 mm x 45 mm (4.0" x 1.77") and a plain mylar mask kit allowing for installation of a wide variety of display boards with the protection of the clear lens and dressed by the mylar frame.
- The lens fits snugly into the case and provides protection from dirt and dust.
- The back of the case has been designed to accept a magnetic strip or "hook & loop" fabric mounting tab (see accessories below).
- The display area has been insert tooled in order to provide the capability of custom molding a low-cost display area to specific requirements.

Accessories

Gasket Kit 1592ETG



Magnetic Mounting Strip 1592ETM



Rubber Feet 1592ETRF



Hook & Loop Mounting Strip 1592ETV



Part Number	Color	Display Cutout	Units	Display Width	Keyboard Width	Length	Enclosure Depth (Includes Lid)
1592ETCDBK	Black	Yes	Inches mm	5.1	3.73	9.21	1.35
1592ETCDGY	Grey						
1592ETSDBK	Black	No	Inches mm	5.1	3.73	9.21	1.35
1592ETSDGY	Grey						



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[1592ETG](#) [1592ETV](#) [1592ETM](#) [1592ETRF](#) [1592RETSDBK](#) [1592ETSDBKRF](#) [1592RETCDBK](#) [1592ETSDGYRF](#)