



Key Features

- One piece molded construction - no lid. Designed for potting box applications.
- Molded from black general purpose ABS plastic.
- Temperature rated -20° to +94° C.
- 1.0 mm (0.04") wall thickness.

Part Number	Package Quantity	Units	Length	Width	Depth
1596B109	1	Inches mm	0.45	0.45	0.35
1596B109-10	10		11.5	11.5	9
1596B110	1	Inches mm	0.85	0.55	0.46
1596B110-10	10		22	14	12
1596B101	1	Inches mm	0.98	0.79	0.59
1596B101-10	10		25	20	15
1596B112	1	Inches mm	0.98	0.98	0.98
1596B112-10	10		25	25	25
1596B102	1	Inches mm	1.18	0.79	0.59
1596B102-10	10		30	20	15
1596B111	1	Inches mm	1.18	1.18	0.79
1596B111-10	10		30	30	20
1596B103	1	Inches mm	1.57	1.37	0.79
1596B103-10	10		40	35	20
1596B107	1	Inches mm	1.57	1.57	0.79
1596B107-10	10		40	40	20
1596B113	1	Inches mm	1.57	1.57	1.15
1596B113-10	10		40	40	29
1596B104	1	Inches mm	1.96	1.57	1.18
1596B104-10	10		50	40	30
1596B108	1	Inches mm	1.96	1.96	1.18
1596B108-10	10		50	50	30
1596B105	1	Inches mm	2.95	1.98	1.39
1596B105-5	5		75	50	35
1596B114	1	Inches mm	2.95	2.95	1.57
1596B114-5	5		75	75	40
1596B115	1	Inches mm	3.5	2.52	1.28
1596B115-5	5		89	64	32.5
1596B106	1	Inches mm	3.93	2.36	0.99
1596B106-5	5		100	60	25

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[1596B104](#) [1596B103](#) [1596B105](#) [1596B107](#) [1596B101](#) [1596B106](#) [1596B109](#) [1596B102](#) [1596B115](#) [1596B112](#)
[1596B111](#) [1596B110](#) [1596B114](#) [1596B113](#) [1596B102-BULK](#) [1596B108](#)