



*Quality Products. Service Excellence.*

## Type 12 Modular Dust-Tight Equipment Cabinet C3 Series

**Note:** This product line has been discontinued as a stocked series. Information is for reference only. For alternative solution assistance, please **contact Hammond here** or call: USA (716) 630-7030, Canada and International (519) 822-2960.



**Note, this product has been discontinued**, but we are still able to manufacture it. **Please contact us** to explore product options.

### Available sizes include:


- **Mounting Heights:**
  - 20U, 24U, 28U, 32U, 36U, 40U, 45U, and 49U
- **Cabinet Width:**
  - 23.00"
- **Cabinet Depth:**
  - We offer flexibility with overall depths from 23.62", up to 48".

### Features

- All frames include four (4) levelling feet and support optional casters.
- Mounting rails are sold separately and are available with square-hole punched or drilled and tapped 10-32.
- Flush-mounted doors with quarter-turn locks are available in solid, **acrylic window**.
- Solid side panels with quarter-turn latch.
- Reinforced solid top panel includes two (2) **lifting eye bolts**.
- One (1) solid interchangeable bottom panel

### Specifications

- Cabinet frame constructed in 14-gauge steel with 12-gauge steel reinforced corner brackets.
- Cabinet doors and side panels are constructed in 16-gauge steel.
- 19" mounting rails are constructed in 12-gauge steel (square hole punched) or 10-gauge steel (drilled and tapped 10-32).
  - Rails include rack unit indicators and are Zinc-plated to provide superior surface areas for equipment grounding.
  - C-channel struts provide cabinet strength, ease and flexibility to adjust mounting rails.
- NEMA Rated for UL 508A Type 12 and CSA Type 12.
  - Complies with NEMA Type 12 and IEC 60529 IP54.
- 1,500 lbs (680 kg) **static load rating**.
- Grounding studs are provided on the frame as well as side panels and doors. The front and rear studs on the cabinet frame conform to PET.
- Finished in textured beige powder paint and can be special ordered in other finishes.
- TAA-compliant for GSA Schedule purchases.
- RoHS Compliant.



C3 Frames (For Reference Only)

Part No.	Overall Dimensions			Usable Mounting Dimensions		Rack Units	Side Panel	Tapped 10-32	Square Hole
	Height	Width	Depth	Height	Depth		(Pair) Part No.	Comination Rail Part No.	L-Panel Rail Part No.
C3F196323CG1	70.31	23.00	23.63	63.06	21.63	36U	C3SP6323CG1	CCR63TZPL	CPR63SZPL
C3F197023CG1	77.31	23.00	23.63	70.06	21.63	40U	C3SP7023CG1	CCR70TZPL	CPR70SZPL
C3F197823CG1	86.06	23.00	23.63	78.81	21.63	45U	C3SP7823CG1	CCR78TZPL	CPR78SZPL
C3F196331CG1	70.31	23.00	31.50	63.06	29.50	36U	C3SP6331CG1	CCR63TZPL	CPR63SZPL
C3F197031CG1	77.31	23.00	31.50	70.06	29.50	40U	C3SP7031CG1	CCR70TZPL	CPR70SZPL
C3F197831CG1	86.06	23.00	31.50	78.81	29.50	45U	C3SP7831CG1	CCR78TZPL	CPR78SZPL

C3 Doors (For Reference Only)

Solid Door With Handle Part No.	Solid Door With Quarter Turn Part No.	Window Door Part No.	Solid Cover Part No.	Use with Cabinet Frame	
				Rack Units	Height
C3DS1963HCG1	C3DS1963QCG1	C3DS1963PCG1	C3CS1963SCG1	36U	63.00
C3DS1970HCG1	C3DS1970QCG1	C3DS1970PCG1	C3CS1970SCG1	40U	70.00
C3DS1978HCG1	C3DS1978QCG1	C3DS1978PCG1	C3CS1978SCG1	45U	78.75

C3 Accessories (For Reference Only)

Baying Kit Beige Part No.	Bottom Plinth Black Part No.	Bottom Plinth Beige Part No.	Caster Kit Part No.	Use with Cabinet Frame		
				Rack Units	Height	Depth
C3JK6323	CPL19423BK1	CPL19423CG1	C3CRS19	36U	63.00	23.63
C3JK7023	CPL19423BK1	CPL19423CG1	C3CRS19	40U	70.00	23.63
C3JK7823	CPL19423BK1	CPL19423CG1	C3CRS19	45U	78.75	23.63
C3JK6331	CPL19431BK1	CPL19431CG1	C3CRS19	36U	63.00	31.50
C3JK7031	CPL19431BK1	CPL19431CG1	C3CRS19	40U	70.00	31.50
C3JK7831	CPL19431BK1	CPL19431CG1	C3CRS19	45U	78.75	31.50

Data subject to change without notice

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[CPL19431CG1](#) [CPL19431BK1](#) [CPL19423CG1](#) [CPL19423BK1](#) [C3CS1963SCG1](#) [C3DS1963HCG1](#) [C3SP6323CG1](#)  
[C3JK7023CG1](#) [CPL19431LG1](#) [C3SP6331CG1](#) [C3F196331CG1](#) [C3F197831CG1](#)