



Quality Products. Service Excellence.

Type 3R Galvanized Wiring Trough C3RWTG Series

NEW

Application

- Designed for use to protect multiple wiring junctions in outdoor environments against the ingress of rain, sleet, snow and the external formation of ice.



Standards

- UL870 Type 3R
- CSA Type 3R
- Complies with
 - NEMA Type 3R
 - IEC 60529, IP24

Construction

- Formed and spot welded from 14 or 16 gauge galvanized steel
- Drip shield top design protects the enclosure against rain, snow or sleet
- Embossed mounting holes on back of enclosure
- Slip on removable front cover is secured with screws
- Padlocking hasp
- To fully comply with UL870 - 2008 requirements a bonding stud is provided on the cover and a ground stud is provided in the enclosure
- A #10 AWG - 12" grounding strap with crimped on ring terminals is also provided to comply with UL requirements



Finish

- Unpainted galvanized steel.

Part No.	Enclosure		
	H	D	L
C3RWT412G	4.00	4.00	12.00
C3RWT418G	4.00	4.00	18.00
C3RWT424G	4.00	4.00	24.00
C3RWT436G	4.00	4.00	36.00
C3RWT448G	4.00	4.00	48.00
C3RWT460G	4.00	4.00	60.00
C3RWT472G	4.00	4.00	72.00
C3RWT612G	6.00	6.00	12.00
C3RWT618G	6.00	6.00	18.00
C3RWT624G	6.00	6.00	24.00
C3RWT636G	6.00	6.00	36.00
C3RWT648G	6.00	6.00	48.00
C3RWT660G	6.00	6.00	60.00
C3RWT672G	6.00	6.00	72.00
C3RWT812G	8.00	8.00	12.00
C3RWT824G	8.00	8.00	24.00
C3RWT836G	8.00	8.00	36.00

Part No.	Enclosure		
	H	D	L
C3RWT872G	8.00	8.00	72.00
C3RWT896G	8.00	8.00	96.00
C3RWT8116G	8.00	8.00	116.00
C3RWT1024G	10.00	10.00	24.00
C3RWT1036G	10.00	10.00	36.00
C3RWT1048G	10.00	10.00	48.00
C3RWT1060G	10.00	10.00	60.00
C3RWT1072G	10.00	10.00	72.00
C3RWT1096G	10.00	10.00	96.00
C3RWT10116G	10.00	10.00	116.00
C3RWT1224G	12.00	12.00	24.00
C3RWT1236G	12.00	12.00	36.00
C3RWT1248G	12.00	12.00	48.00
C3RWT1260G	12.00	12.00	60.00
C3RWT1272G	12.00	12.00	72.00
C3RWT1284G	12.00	12.00	84.00
C3RWT1296G	12.00	12.00	96.00

Part No.	Enclosure		
	H	D	L
C3RWT848G	8.00	8.00	48.00
C3RWT860G	8.00	8.00	60.00

Part No.	Enclosure		
	H	D	L
C3RWT12116G	12.00	12.00	116.00

Tags: **Type 3R, NEMA 3R, outdoor, wiring, trough, galvanized steel**

Data subject to change without notice

© 2024. Hammond Manufacturing Ltd. All rights reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[C3RWT10116G](#) [C3RWT1024G](#) [C3RWT1036G](#) [C3RWT1048G](#) [C3RWT1060G](#) [C3RWT1072G](#) [C3RWT1096G](#)
[C3RWT12116G](#) [C3RWT1224G](#) [C3RWT1236G](#) [C3RWT1248G](#) [C3RWT1260G](#) [C3RWT1272G](#) [C3RWT1284G](#)
[C3RWT1296G](#) [C3RWT412G](#) [C3RWT418G](#) [C3RWT424G](#) [C3RWT436G](#) [C3RWT448G](#) [C3RWT460G](#) [C3RWT472G](#)
[C3RWT612G](#) [C3RWT618G](#) [C3RWT624G](#) [C3RWT636G](#) [C3RWT648G](#) [C3RWT660G](#) [C3RWT672G](#) [C3RWT8116G](#)
[C3RWT812G](#) [C3RWT824G](#) [C3RWT836G](#) [C3RWT848G](#) [C3RWT860G](#) [C3RWT872G](#) [C3RWT896G](#)