




Quality Products. Service Excellence.

Colo Cabinet *CL Series*

 **Note:** This product line has been discontinued as a stocked series. Information is for reference only. It has been replaced with **CLC Series**. For alternative solution assistance, **contact Hammond here** or call: USA (716) 630-7030, Canada and International (519) 822-2960.



Features:

- One single frame allows multiple bay configurations. Mounting space includes:
 - 1-Bay = 44U, 2-Bay = 21U, 3-Bay = 14U, 4-Bay = 10U
- Standard available configurations available in 36" and 42" depths.
- Vented shelves include rear removable panels for vertical PDU installations.
- Front and Rear Perforated Doors with 65% air flow.
- Doors include 4-pin combination lock with key override.
- Vertical Cable Managers can be installed either top or bottom. Designed to accommodate sliding rail mount kit on servers.
- Cabinet top includes removable top panel and provisions for containment system and cable trough accessories.



Specifications:

- 14-gauge welded steel frame; 16-gauge doors and side panel.
- Adjustable depth EIA-Compliant Adjustable depth mounting rails.
- Available as Square Hole or Tapped (10-32) mounting rail.
- Rugged textured black powder paint
- Tested to nearly double the suggested load rating of 1,800 lbs.
- RoHS Compliant.
- Manufactured in North America.

Additional Accessories:

- Third set of rails can easily be added with either 10-32 taps or square holes.
- Security upgrade kit ensures entire cabinet is tamper-proof.
- Bay upgrade kit divides a single bay into a 2, 3 or 4 bay cabinet.
- Right-hand door hinge kit.

Gallery



Data subject to change without notice

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Hammond:

[CLSECUPG](#) [CLB2442BK](#) [CLF244442BK](#) [CLB2436BK](#) [CLSP4442BK](#) [CLRHHNG](#) [CLTROUGH](#) [CLSP4436BK](#)
[CLF244436BK](#)