



Quality Products. Service Excellence.

Type 1 Mild Steel Splitter Trough *CST Series*

Hinged Door with Screw

Application

- The splitter troughs are designed for distribution of up to 600 A (max) service using either 3 or 4 wires. 75° C conductor ampacity permitted.



Standards

- CSA Certified
- Complies with
 - IEC 60529, IP20

Construction

- Formed and spot welded from 16 gauge steel. When width is 8" or more, 14 gauge.
- Factory installed splitter blocks.
- Series of knockouts on each side.
- Padlocking hasp.



Finish

- Cover and enclosure are finished in recoatable smooth ANSI 61 gray powder coating.

Accessories

- Splitter Blocks
- Grounding Kits

New and improved PDF part drawing files with more detail now available.

Click part number in table below to access PDF, DXF, and STEP files.

3 Wire Part No.	4 Wire Part No.	Less Blocks Part No.	CUI/AL Amps	Dimensions H W D			Splitter Block Reference
CST273	CST274	-	70/70	24.00	6.00	4.00	CSBL125T
CST373	CST374	-	70/70	36.00	6.00	4.00	CSBL125T
CST473	CST474	-	70/70	48.00	6.00	4.00	CSBL125T
CST2103	CST2104	CST2100	125/120	24.00	6.00	4.00	CSBL125T
CST3103	CST3104	CST3100	125/120	36.00	6.00	4.00	CSBL125T
CST4103	CST4104	CST4100	125/120	48.00	6.00	4.00	CSBL125T
CST6103*	CST6104*	CST6100*	125/120	72.00	8.00	5.00	CSBL125T
CST2203*	-	CST2200*	225/225	24.00	8.00	5.00	CSBL225
CST3203*	CST3204*	CST3200*	225/225	36.00	8.00	5.00	CSBL225
CST4203*	CST4204*	CST4200*	225/225	48.00	8.00	5.00	CSBL225
CST5203*	CST5204*	CST5200*	225/225	60.00	8.00	5.00	CSBL225
CST6203*	CST6204*	-	225/225	72.00	8.00	5.00	CSBL225

3 Wire	4 Wire	Less Blocks	CU/AL	Dimensions			Splitter
Part No.	Part No.	Part No.	Amps	H	W	D	Block Reference
CST3403*	-	CST3400*	400/400	36.00	10.00	6.00	CSBL400
CST4403*	CST4404*	CST4400*	400/400	48.00	10.00	6.00	CSBL400
CST5403*	CST5404*	CST5400*	400/400	60.00	10.00	6.00	CSBL400
CST6403*	CST6404*	CST6400*	400/400	72.00	10.00	6.00	CSBL400
CST4603*	CST4604*	-	600/600	48.00	10.00	6.00	CSBL600
CST5603*	CST5604*	-	600/600	60.00	10.00	6.00	CSBL600
CST6603*	CST6604*	-	600/600	72.00	10.00	6.00	CSBL600

* 14 gauge steel

Tags: CST, trough, splitter, knockouts, 3 wire, 4 wire, steel

Data subject to change without notice

© 2025. Hammond Manufacturing Ltd. All rights reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[CST5200](#) [CST3400](#) [CST5603](#) [CST3403](#) [CST6404](#) [CST6204](#) [CST3103](#) [CST5203](#) [CST4604](#) [CST6400](#) [CST5404](#)
[CST6104](#) [CST4100](#) [CST4400](#) [CST5204](#) [CST6103](#) [CST5604](#) [CST4403](#) [CST6603](#) [CST3200](#) [CST4203](#) [CST4204](#)
[CST3100](#) [CST6403](#) [CST274](#) [CST4103](#) [CST474](#) [CST3203](#) [CST6604](#) [CST4404](#) [CST2104](#) [CST374](#) [CST473](#)
[CST3204](#) [CST5400](#) [CST2200](#) [CST6203](#) [CST4104](#) [CST2100](#) [CST273](#) [CST3104](#) [CST2203](#) [CST4603](#) [CST2103](#)
[CST4200](#) [CST373](#) [CST5403](#) [CST6100](#)