



Quality Products. Service Excellence.

Fan Cords *DNFC Series*

Features



- For wiring of tube axial fans (above)
- Molded female standard fan plug (0.91" x 0.68")
- SPT-1 x 18/2 type wire cord, rated 300V and 105 degrees C
- **DNFC48P** is the fan cord required for a longer connection wire for **DNFK2AC120** and **AVFK2AC120**.
- See the tables below for detailed descriptions

Gallery



Accessories

- Tube Axial Fans
- Metal Fan Guard

Part Number	Description	Lead Length	Fan Connector	115VAC Plug
DNMFC	Single	24.00	45 degree	No
DNFC48P	Single	48.00	45 degree	Yes
DNFC72P	Single	72.00	45 degree	No
DNFC72PG	Single	72.00	45 degree	Yes
DNFCDC2P	Daisy Chain	24.00	Qty 2-45 degree, 12" apart	Yes
DNFCDC3P	Daisy Chain	24.00	Qty 3-45 degree, 12" apart	No
DNFCDC3PG	Daisy Chain	24.00	Qty 3-45 degree, 12" apart	Yes

Data subject to change without notice

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[DNFC72P](#) [DNFC48P](#) [DNFCDC3P](#) [DNFCDC2P](#) [DNMFC](#) [DNFC72PG](#) [DNFCDC3PG](#)